

# KERN ABT 120-5DNM

The premium model with single-cell weighing system



Automatic adjustment - Standard temperature deviation	0,5 °C
Automatic adjustment - Standard time interval	4 h
Stabilization time	10 s; 4 s
Warm-up time	8 h; 8 h
Eccentric loading at 1/3 [Max]	0,00009 g; 0,0003 g

## Approval

CE mark	✓
Accuracy classe	I
Verification scale interval [e]	0,001 g; 0,001 g
Verification scale interval [e] (ct)	0,01 ct; 0,01 ct
Conformity assessment possible ex works	✓

## Display

Display type	LCD
Display digit height	14 mm

## Construction

Dimension housing (W×D×H)	215×340×335 mm
Dimensions rectangular draught shield - inner (W×D×H)	168×172×223 mm
Dimensions rectangular draught shield - outer (W×D×H)	200×240×260 mm
Material display housing	Plastics
Material housing	metal
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	80 mm
Levelling feet adjustable	✓

## Functions

Number of keys for operation	6
Capacity - Display	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Recipe/summing level	Rez A (Net total)
Sum memory function	✓
Underfloor weighing	Hook (included in delivery)
Interfaces	RS-232 standard

## Category

Brand	KERN
Product category	Laboratory balance
Product group	Analytical balance
Product family	ABT

## Measuring System

Construction type of the scale	Multi-range balance
Weighing system	Single-Cell
Weighing capacity [Max]	42 g; 120 g
Weighing capacity [Max] (ct)	210,045 ct; 600 ct
Readability [d]	0,00001 g; 0,0001 g
Readability carat [d] (ct)	0,0001 ct; 0,001 ct
Resolution	4.200.000, 1.200.000
Linearity	± 0,00003 g; 0,0002 g
Reproducibility	0,00002 g; 0,0001 g
Tare range	120 g
Default unit	g
Units	g ct
Units (if device is conformity assessed)	g ct
Minimum weight [Min]	0,001 g
USP Minimum weight of sample (k = 2, U = 0.1%)	40 mg
Minimum weight [Min] (ct)	0,01 ct
Adjustment options	Adjusting with external weight Internal calibration (automatic) Adjusting with internal weight (manual)

# KERN ABT 120-5DNM

# KERN

The premium model with single-cell weighing system

## Counting

Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Counting reference weight can be entered	✓
Reference quantity	10, 20, 50, 100
Counting resolution (laboratory conditions)	120.000

## Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
	EURO
Plug-in power supply / adapter for countries - included with the delivery	AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	430×685×650 mm
Net weight	7,5 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	13 kg
Shipping weight	38,3 kg

## Services (optional)

Article number for conformity assessment	965-201
--	---------

Article number for DAkkS calibration 963-101

Article number for certificate of conformity (verification) 969-517

## Pictograms

### STANDARD



### OPTION



### FACTORY

