

# KERN AD 9030

**KERN**

Screw Tension Clamp for laboratory tensile force measurements



## Category

Brand	Sauter
Product category	Clamp
Product group	Screw tension clamp

## Construction

Dimensions completely mounted (W×D×H)	120×75×30 mm
Material	aluminium
Mounting - force dissipation	Threaded hole M6 External thread M12
Tensile/compressive force [Max]	2,5 kN
Maximum clamp width	100 mm
Clamping width	10 mm

## Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	14 d
Dimensions packaging (W×D×H)	120×75×30 mm
Net weight	0,6 kg
Shipping method	Parcel service
Net weight approx.	0,60 kg
Gross weight approx.	0,60 kg
Shipping weight	0,6 kg

## Pictograms