

KERN CD 20-2P2

KERN

Loadcell made of stainless steel



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CD P2

Measuring System

Weighing capacity [Max]	20000 kg
Load cell connection	4-wire
Load cell OIML class	C2
Load cell - Resolution (verifiable)	2000 e
Load cell - characteristic value - nominal	1,5 mV/V
Load cell - characteristic value - variance	0,002 mV/V
Load cell - Y-value	5000
Load cell - Combined error	0,03%
Load cell - Dead load [Min] (%)	0%
Measuring applications	force mass
Load cell - Input resistance - nominal	700 Ω
Load cell - Output resistance - nominal	703 Ω
Load cell - Isolation resistance - [Min]	5000 M Ω
Load cell - Recommended excitation voltage [Min]	5 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Input resistance - variance	7 Ω

Load cell - Output resistance - variance	4 Ω
Measuring range force [Max] (N)	200 kN
Directions of force	tension compression

Approval

CE mark	✓
---------	---

Construction

Design	Tension-/compression rod
Material	stainless steel
Cable length	20 m
Mounting - force application	External thread M36 \times 3
Mounting - force dissipation	External thread M36 \times 3

Functions

IP protection - complete device	IP68
---------------------------------	------

Environmental conditions

Use temperature [Min]	-10 $^{\circ}$ C
Use temperature [Max]	40 $^{\circ}$ C
Ambient temperature [Min]	-35 $^{\circ}$ C
Ambient temperature [Max]	65 $^{\circ}$ C
Storage temperature [Min]	-40 $^{\circ}$ C
Storage temperature [Max]	70 $^{\circ}$ C

Packing & Shipping

Readability force [d] (N)	36 d
Dimensions packaging (WxDxH)	220 \times 220 \times 160 mm
Net weight	2,2 kg
Shipping method	Parcel service
Net weight approx.	2,2 kg
Gross weight approx.	2,8 kg
Shipping weight	2,7 kg

Pictograms

STANDARD



OPTION

