

KERN CD 20-3P1

KERN

Loadcell made of stainless steel



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CD P1

Measuring System

Weighing capacity [Max]	20000 kg
Load cell connection	4-wire
Load cell OIML class	C3
Load cell - Resolution (verifiable)	3000 e
Load cell - characteristic value - nominal	2 mV/V
Load cell - characteristic value - variance	0,002 mV/V
Load cell - Y-value	10000
Load cell - Combined error	0,023%
Load cell - Dead load [Min] (%)	0%
Measuring applications	force mass
Load cell - Input resistance - nominal	700 Ω
Load cell - Output resistance - nominal	703 Ω
Load cell - Isolation resistance - [Min]	5000 M Ω
Load cell - Recommended excitation voltage [Min]	5 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Input resistance - variance	7 Ω

Load cell - Output resistance - variance	4 Ω
Measuring range force [Max] (N)	200 kN
Directions of force	compression

Approval

CE mark	✓
---------	---

Construction

Design	Load cell
Material	stainless steel
Cable length	15 m
Dimension ($\varnothing \times H$)	88,9 \times 118,5 mm
Mounting - force application	Pressure piece
Mounting - force dissipation	Pressure piece

Functions

IP protection - complete device	IP68
---------------------------------	------

Environmental conditions

Use temperature [Min]	-10 $^{\circ}$ C
Use temperature [Max]	40 $^{\circ}$ C
Ambient temperature [Min]	-35 $^{\circ}$ C
Ambient temperature [Max]	65 $^{\circ}$ C
Storage temperature [Min]	-40 $^{\circ}$ C
Storage temperature [Max]	70 $^{\circ}$ C

Packing & Shipping

Readability force [d] (N)	2 d
Dimensions packaging (WxDxH)	220 \times 220 \times 160 mm
Net weight	2,2 kg
Shipping method	Parcel service
Net weight approx.	2,2 kg
Gross weight approx.	2,8 kg
Shipping weight	2,7 kg

Pictograms

STANDARD

