

Load Cells SAUTER CK P1-P4 · CK Y1 · CK Y4 · CD P1









1 SAUTER CE P4136

CK P1-P4 Miniature load cells made of aluminium

CK Y1 · Y4 Flat miniature alloy steel load cells

CD P1 Load cells made of stainless steel

Technical data

- Dust and spray protection to IP65 (in accordance with EN 60529)
- Aluminium
- · High level of accuracy
- · Suitable for small scales and kitchen scales and force-measuring devices
- · 4-wire connection
- · Cable length approx. 0,25 m

Technical data

CK Y4

- · Accuracy class in accordance with OIML C1
- · RoHS compliant
- High precision (comprehensive Error 0,05 % F.S.)
- · Very low design
- Suitable for e.g. personal scales, kitchen scales, post scales or other scales with lowest installation height
- · Cable length approx. 0,45 m

CK Y1:

- · Protection against dust and water splashes IP66
- Scope of delivery: 1 piece
- · Full-bridge circuit (Junction box required for connecting several load cells)

CK Y4:

- · Protection against dust and water splashes IP65
- · Scope of delivery: 1 set (4 pieces)
- Quarter-bridge circuit: 4 load cells are connected to a full-bridge
- · No junction box required
- · Corner adjustment not possible

Technical data

- Accuracy in accordance with OIML R60 C3
- · RoHS compliant
- Dust and spray protection to IP68 (in accordance with EN 60529), hermetically encapsulated
- · Stainless steel
- · Area of application: Weight measurement as well as compressive force
- · Suitable for vehicle scales, funnel scales, vehicle testing equipment, test stands
- · Note: EX version or accuracy class C4 on request
- · Nominal sensitivity: 2 mV/V
- Cable length approx. 15 m

Accessories CD P1:

- · Pressure piece, steel, rustproof, suitable for CD 10-3P1, CD 20-3P1, SAUTER CE P10330
- · Pressure piece, steel, rustproof, suitable for CD 40-3P1, CD 50-3P1, SAUTER CE P10350
- Mounting kit, steel, rustproof, suitable for CD 10-3P1, CD 20-3P1, SAUTER CE P41430
- · Mounting kit, steel, rustproof, suitable for CD 40-3P1, CD 50-3P1, SAUTER CE P14150

Tip

Further details and technical data sheet as well as an extensive range of accessories can be found at

STANDARD









Model	Nominal load	Compre- hensive Error	
SAUTER	kg		
CK 600-0P1	0,6	0,03 %	
CK 1-0P1	1	0,03 %	
CK 2-0P1	2	0,03 %	
CK 3-0P1	3	0,03 %	
CK 5-0P1	5	0,03 %	
CK 6-0P1	6	0,03 %	
CK 300-0P2*	0,3	0,03 %	
CK 600-0P2*	0,6	0,03 %	
CK 100-0P4*	0,1	0,05 %	
CK 120-0P4*	0,12	0,05 %	
CK 300-0P4	0,3	0,05 %	
CK 500-0P4	0,5	0,05 %	

■ * ONLY WHILE STOCKS LAST!



Model	Nominal load	
SAUTER	kg	
CK 10-Y1	10	
CK 30-Y1	30	
CK 10-Y4	10	
CK 30-Y4	30	
CK 50-Y4	50	

STANDARD



Model Nominal load

SAUTER

CD 10-3P1	10 t/100 kN	
CD 20-3P1	20 t/200 kN	
CD 40-3P1	40 t/400 kN	
CD 50-3P1	50 t/500 kN	

* up to max. 25 t/250 kN

■ ONLY WHILE STOCKS LAST!

MEASURING TECHNOLOGY & TEST SERVICE 2024

SAUTER Pictograms



Conformity assessment

Models with type approval

DAkkS calibration

The time required for

DAkkS calibration is shown

Factory calibration (ISO)

The time required for factory

calibration is specified in

Package shipment

The time required for

internal shipping prepara-

tions is shown in days in

the pictogram

the pictogram

the pictogram

Pallet shipment

The time required for

internal shipping prepara-

tions is shown in days in

in days in the pictogram

systems

possible

for construction of verifiable

M

DAkkS

+3 DAYS

ISO

1 DAY



Adjusting program (CAL)

For quick setting of the instrument's accuracy. External adjusting weight required



Calibration block

Standard for adjusting or correcting the measuring



Peak hold function

Capturing a peak value within a measuring process



Scan mode

Continuous capture and display of measurements



Push and Pull

The measuring device can capture tension and compression forces



Length measurement

Captures the geometric dimensions of a test object or the movement during a test process



Focus function

Increases the measuring accuracy of a device within a defined measuring range



Internal memory

To save measurements in the device memory



Data interface RS-232

Bidirectional, for connection of printer and PC



Profibus

For transmitting data, e.g. between scales, measuring cells, controllers and peripheral devices over long distances. Suitable for safe, fast, fault-tolerant data transmission. Less susceptible to magnetic interference



Profinet

Enables efficient data exchange between de-centralised peripheral devices (balances, measuring cells, measuring instruments etc.) and a control unit (controller). Especially advantageous when exchanging complex measured values, device, diagnostic and process information. Savings potential through shorter commissioning times and device integration possible



Data interface USB

To connect the measuring instrument to a printer, PC or other peripheral devices



Bluetooth* data interface

To transfer data from the balance/measuring instrument to a printer, PC or other peripherals



WIFI data interface

To transfer data from the balance/measuring instrument to a printer, PC or other peripherals



Data interface infrared

To transfer data from the measuring instrument to a printer, PC or other peripheral devices



Control outputs (optocoupler, digital I/O) To connect relays, signal

lamps, valves, etc.



Analogue interface

To connect a suitable peripheral device for analogue processing of the measurements



Analogue output

For output of an electrical signal depending on the load (e.g. voltage 0 V - 10 V or current 4 mA - 20 mA)



Statistics

Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software

To transfer the measurement data from the device to a PC



Printer

A printer can be connected to the device to print out the measurement data



Network interface

For connecting the scale/ measuring instrument to an Ethernet network



KERN Communication Protocol (KCP)

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO record keeping

of measurement data with date, time and serial number. Only with SAUTER printers



Measuring units

Weighing units can be switched to e.g. non-metric. Please refer to website for more details



Measuring with tolerance range (limit-setting function)

Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model



Protection against dust and water splashes IPxx

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989 +A1:1999+A2:2013



ZERO

Resets the display to "0"



Battery operation

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack

Rechargeable set



Plug-in power supply 230V/50Hz in standard

version for EU. On request GB, AUS or US version available



Integrated power supply unit

Integrated, 230V/50Hz in EU. More standards e.g. GB, AUS or US on request



Motorised drive

The mechanical movement is carried out by a electric motor



Motorised drive

The mechanical movement is carried out by a synchronous motor (stepper)



Fast-Move

The total length of travel can be covered by a single lever movement



The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license Other trademarks and trade names are those of their respective owners