

KERN CK 300-0P4

KERN

Miniature load cell made of aluminium



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load cell
Product family	CK P4

Measuring System

Weighing capacity [Max]	300 g
Load cell connection	4-wire
Load cell OIML class	C1
Load cell - characteristic value - nominal	0,9 mV/V
Load cell - characteristic value - variance	0,18 mV/V
Load cell - Combined error	0,05%
Load cell - Dead load [Min] (%)	0%
Measuring applications	mass
Load cell - Input resistance - nominal	1055 Ω
Load cell - Output resistance - nominal	1000 Ω
Load cell - Isolation resistance - [Min]	2000 M Ω
Load cell - Recommended excitation voltage [Min]	2 V
Load cell - Recommended excitation voltage [Max]	5 V
Load cell - Input resistance - variance	10 Ω
Load cell - Output resistance - variance	10 Ω
Directions of force	compression

Approval

CE mark	✓
---------	---

Construction

Design	Miniature bending beam
Dimension (W×D×H)	47×20×6,6 mm
Material	aluminium
Cable length	0,25 m
Mounting - force application	2 × through hole \varnothing 3,0 mm
Mounting - force dissipation	2 × threaded hole M3

Functions

IP protection - complete device	IP65
---------------------------------	------

Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	40 °C
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	65 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	145×60×35 mm
Net weight	0,01 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,40 kg
Shipping weight	0,37 kg

Services (optional)

Article number for DAkkS calibration (compressive force)	963-261V
--	----------

Pictograms

STANDARD



OPTION

