

# KERN CO 20-Y1

# KERN

Miniature cylindrical load cell made from stainless steel



## Construction

Design	Load cell
Material	stainless steel
Cable length	2 m
Dimension (Ø×H)	20×12 mm
Mounting - force application	Thrust piece (from customer side)
Mounting - force dissipation	3 × threaded hole M3

## Functions

IP protection - complete device	IP65
---------------------------------	------

## Environmental conditions

Use temperature [Min]	0 °C
Use temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	120×90×85 mm
Net weight	0,049 kg
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,10 kg
Shipping weight	0,2 kg

## Services (optional)

Article number for DAkkS calibration (compressive force)	963-261V
--	----------

## Pictograms

### STANDARD



### OPTION



## Category

Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CO Y1

## Measuring System

Weighing capacity [Max]	20 kg
Load cell connection	4-wire
Load cell OIML class	G5
Load cell - characteristic value - nominal	1 mV/V
Load cell - Combined error	0,5%
Measuring applications	force mass
Load cell - Input resistance - nominal	350 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Recommended excitation voltage [Min]	9 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Input resistance - variance	20 Ω
Load cell - Output resistance - variance	3 Ω
Measuring range force [Max] (N)	200 N
Directions of force	compression

## Approval

CE mark	✓
---------	---