

Load Cells SAUTER CP P4 · CP Y4 · CP P1 · CP Y1 · CP P3







CP P4 · CP Y4 Single-point load cells made of anodised aluminium

Technical data

- CP P4: Accuracy in accordance with OIML R60 C3
- · CP Y4: Accuracy in accordance with OIML R60 C2
- · CE and RoHS compliant
- Dust and spray protection to IP65 (in accordance with EN 60529)
- · Aluminium, anodised
- Suitable for price-computing scales, bench scales, platform scales, etc.
- Maximum platform size 200×200 mm
- · 4-wire connection
- Nominal sensitivity: 0,9 mV/V
- · Cable length approx. 0,4 m

CP P1 · CP Y1 Single-point load cells made of anodised aluminium

Technical data

- · CP P1: Accuracy in accordance with OIML R60 C3
- CP Y1: Accuracy in accordance with OIML R60 C2
- CE and RoHS compliant
- Dust and spray protection to IP65 (in accordance with EN 60529)
- · Aluminium, anodised
- · Suitable for price-computing scales, bench scales, platform scales, etc.
- Maximum platform size 250×350 mm
- · 4-wire connection

Model

- Nominal sensitivity: 2 mV/V
- · Note: Version in accordance with OIML R60 C4 or C5 on request

Nominal Cable

CP P3 Single-point load cells made of anodised aluminium

Technical data

- · Accuracy in accordance with OIML R60 C3
- · CE and RoHS compliant
- · Dust and spray protection to IP65 (in accordance with EN 60529)
- · Suitable for price-computing scales, bench scales, platform scales, etc.
- Maximum platform size 350×400 mm
- · 4-wire connection
- · Nominal sensitivity: 2 mV/V
- · Note: Version in accordance with OIML R60 C4 on request
- · Cable length approx. 3 m

STANDARD



CP 600-0P4







Model	Nominai ioad	
SAUTER	kg	
CP 300-0P4	0.3	

0,6

Model	Nominal	load

SAUTER	kg	
ECO design		
CP 300-0Y4	0,3	
CP 1500-0Y4	1,5	
CP 3000-0Y4	3	

STANDARD OPTION М

	load	length	
SAUTER	kg	m	
CP 3-3P1	3	0,4	
CP 3-2-3P1	3	2	
CP 5-3P1	5	0,4	
CP 6-3P1	6	0,4	
CP 8-3P1	8	0,4	
CP 10-3P1	10	0,4	
CP 10-3-3P1	10	3	
CP 15-3P1	15	0,4	
CP 15-3-3P1	15	3	
CP 20-3P1	20	0,4	
CP 30-3P1	30	0,4	
CP 35-3P1	35	0,4	
CP 35-3-3P1	35	3	
CP 40-3P1	40	0,4	
CP 50-3P1	50	0,4	
CP 50-2-3P1	50	2	
Nous mandal			

New model

Nominal Cable Model load length

SAUTER	kg	m			
ECO design (without EC type approval)					
CP 3-2Y1	3	0,4			
CP 5-2Y1	5	0,4			
CP 10-2Y1	10	0,4			
CP 15-2Y1	15	0,4			
CP 20-2Y1	20	0,4			
CP 30-2Y1	30	0,4			



Model

SAUTER kg CP 30-3P3 30 CP 40-3P3 40 CP 50-3P3 50 CP 75-3P3 75 CP 100-3P3 100

Nominal load

Tip



MEASURING TECHNOLOGY & TEST SERVICE 2024

SAUTER Pictograms



Conformity assessment

Models with type approval

DAkkS calibration

The time required for

DAkkS calibration is shown

Factory calibration (ISO)

The time required for factory

calibration is specified in

Package shipment

The time required for

internal shipping prepara-

tions is shown in days in

the pictogram

the pictogram

the pictogram

Pallet shipment

The time required for

internal shipping prepara-

tions is shown in days in

in days in the pictogram

systems

possible

for construction of verifiable

M

DAkkS

+3 DAYS

ISO

1 DAY



Adjusting program (CAL)

For quick setting of the instrument's accuracy. External adjusting weight required



Calibration block

Standard for adjusting or correcting the measuring



Peak hold function

Capturing a peak value within a measuring process



Scan mode

Continuous capture and display of measurements



Push and Pull

The measuring device can capture tension and compression forces



Length measurement

Captures the geometric dimensions of a test object or the movement during a test process



Focus function

Increases the measuring accuracy of a device within a defined measuring range



Internal memory

To save measurements in the device memory



Data interface RS-232

Bidirectional, for connection of printer and PC



Profibus

For transmitting data, e.g. between scales, measuring cells, controllers and peripheral devices over long distances. Suitable for safe, fast, fault-tolerant data transmission. Less susceptible to magnetic interference



Profinet

Enables efficient data exchange between de-centralised peripheral devices (balances, measuring cells, measuring instruments etc.) and a control unit (controller). Especially advantageous when exchanging complex measured values, device, diagnostic and process information. Savings potential through shorter commissioning times and device integration possible



Data interface USB

To connect the measuring instrument to a printer, PC or other peripheral devices



Bluetooth* data interface

To transfer data from the balance/measuring instrument to a printer, PC or other peripherals



WIFI data interface

To transfer data from the balance/measuring instrument to a printer, PC or other peripherals



Data interface infrared

To transfer data from the measuring instrument to a printer, PC or other peripheral devices



Control outputs

(optocoupler, digital I/O)
To connect relays, signal lamps, valves, etc.



Analogue interface

To connect a suitable peripheral device for analogue processing of the measurements



Analogue output

For output of an electrical signal depending on the load (e.g. voltage 0 V - 10 V or current 4 mA - 20 mA)



Statistics

Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software

To transfer the measurement data from the device to a PC



Printer

A printer can be connected to the device to print out the measurement data



Network interface

For connecting the scale/ measuring instrument to an Ethernet network



KERN Communication Protocol (KCP)

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO record keeping

of measurement data with date, time and serial number. Only with SAUTER printers



Measuring units

Weighing units can be switched to e.g. non-metric. Please refer to website for more details



Measuring with tolerance range (limit-setting function)

Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model



Protection against dust and water splashes IPxx

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989 +A1:1999+A2:2013



ZERO

Resets the display to "0"



Battery operation

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack

Rechargeable set



Plug-in power supply 230V/50Hz in standard

version for EU. On request GB, AUS or US version available



Integrated power supply unit

Integrated, 230V/50Hz in EU. More standards e.g. GB, AUS or US on request



Motorised drive

The mechanical movement is carried out by a electric motor



Motorised drive

The mechanical movement is carried out by a synchronous motor (stepper)



Fast-Move

The total length of travel can be covered by a single lever movement



The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license Other trademarks and trade names are those of their respective owners