

KERN DC 1-Y2

KERN

Static torque sensor made from alloy steel



Construction

Design	round
Material	steel
Cable length	2 m
Mounting - force application	12,5 mm outer square
Mounting - force dissipation	4 × through hole Ø 6,5 mm

Functions

IP protection - complete device	IP65
---------------------------------	------

Environmental conditions

Use temperature [Min]	-20 °C
Use temperature [Max]	65 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	120×90×85 mm
Net weight	0,321 kg
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	0,35 kg
Shipping weight	0,326 kg

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Measuring cell
Product group	Torque sensor
Product family	DC Y2

Measuring System

Load cell connection	4-wire
Load cell - characteristic value - nominal	1,5 mV/V
Load cell - characteristic value - variance	0,15 mV/V
Load cell - Combined error	0,5%
Measuring applications	static torque
Load cell - Input resistance - nominal	380 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Isolation resistance - [Min]	5000 MΩ
Load cell - Recommended excitation voltage [Min]	9 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Input resistance - variance	10 Ω
Load cell - Output resistance - variance	3 Ω
Measuring range torque [Max]	1 Nm

Approval

CE mark	✓
---------	---