


Industrial Platform Scale KERN EOC



# Robust and high-resolution platform scale with practical Flip/Flop display device for greatest ease of use







Practical Flip/Flop display device: flexible positioning e.g. free-standing or screwed to the wall (optional). By rotating the upper housing shell you can determine the angle of the display as well as the cable outlet. Factory Option for an additional cost, delivery time + 2 working days, KERN KIB-M01, see Accessories on the right, please indicate when placing your order

#### Industrial Platform Scale KERN EOC



#### **Features**

- · High mobility: thanks to rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations (laboratory, production, quality control, commissioning etc.)
- • Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65. Level indicator and levelling feet for precise levelling of the scale, fitted as standard, to give the most accurate weighing result
- · Weighing with tolerance range (checkweighing): a visual and audible signal helps with portioning, dispensing or grading
- · Hold function: When the weighing conditions are unstable, a stable weight is calculated determining an average value
- · Benchtop stand incl. wall mount for display device as standard



- · Protective working cover included with delivery
- · Searching and remote control of the balance using external control devices or computers with the KERN Communication Protocol (KCP). KCP is a standardised interface command structure for KERN balances and other instruments which allows you to recall and manage all relevant parameters and device functions. You can therefore simply connect KERN devices with KCP to computers, industrial control systems and other digital systems. In a large number of cases the KCP is compatible with the MT-SICS protocol.

#### Technical data

- A 300×300×110 mm B 500×400×120 mm
- **©** 600×500×150 mm **D** 950×500×60 mm
- · Dimensions of display device W×D×H 268×115×80 mm



• Permissible ambient temperature -10 °C/40 °C

#### Accessories

- · Protective working cover, scope of delivery 5 items, KERN EOC-A01S05
- · Internal rechargeable battery pack, operating time up to 43 h without backlight, charging time approx. 3 h, KERN KFB-A01
- 2 for models with weighing plate size A C: Stand to be screwed onto the platform, height of stand approx.330 mm, KERN EOC-A05
- 3 Mount to fasten the display device to the platform, KERN EOC-A03
- Benchtop stand incl. wall mount for display device, KERN EOC-A04
- Modification of the display device, to move the cable outlet to the front of the display device, ideal e.g. for subsequent wall installation of the display device (standard configuration ex works: rear outlet), Factory Option, delivery time
- + 2 working days, KERN KIB-M01

DAkkS

- · Large backlit LCD display, digit height 25 mm
- · Weighing plate dimensions, stainless steel, W×D×H

CAL EXT RS 232	ROTOCOL PRINTER PO	CS SUM PERCEN	TOL MOVE	IP 65 MULT	I DMS 1 DAY	ACCU +	3 DAYS		
				1					
Model	Weighing	Readability	Repro-	Linearity	Smallest part	Cable length	Net weight	Weighing	Options
	capacity		ducibility		weight	spiral cable*		plate	DAkkS Calibr. Cert.
	[Max]	[d]			(Normal)	approx.	approx.		DAkkS
KERN	kg	g	g	g	g/piece	m	kg		KERN
Multi-range balance with high-resolution display, with increasing load it switches automatically to the next largest weighing range [Max] and readout [d]									
and when the load is fully removed, the balance switches back to the lower range									
EOC 10K-4	6   15	0,2   0,5	0,2   0,5	± 0,6   1,5	5	3	6	Α	963-128
EOC 30K-4	15   35	0,5   1	0,5   1	± 1,5   3	10	3	9	В	963-128
EOC 30K-4S	15   35	0,5   1	0,5   1	± 1,5   3	10	3	6	Α	963-128
EOC 60K-3	30   60	1   2	1   2	± 3   6	20	3	7	Α	963-129
EOC 60K-3L	30   60	1   2	1   2	±3   6	20	3	9	В	963-129
EOC 100K-3	60   150	2   5	2   5	± 6   15	50	3	6	Α	963-129
EOC 100K-3L	60   150	2   5	2   5	± 6   15	50	3	9	В	963-129
EOC 300K-3	150   300	5   10	5   10	± 15   30	100	3	9	В	963-129
Multi-range balance without high-resolution display									
EOC 6K-3	3   6	1   2	1   2	±3   6	2,5	3	6	Α	963-128
EOC 10K-3	6   12	2   5	2   5	± 6   15	5	3	6	Α	963-128
EOC 30K-3	15   35	5   10	5   10	± 15   30	10	3	6	Α	963-128
EOC 30K-3L	15   35	5   10	5   10	± 15   30	10	3	9	В	963-128
EOC 60K-2	30   60	10   20	10   20	± 30   60	20	3	7	Α	963-129
EOC 60K-2L	30   60	10   20	10   20	± 30   60	20	3	9	В	963-129
EOC 100K-2	60   150	20   50	20   50	± 60   150	50	3	6	Α	963-129
EOC 100K-2L	60   150	20   50	20   50	± 60   150	50	3	9	В	963-129
EOC 100K-2XI	. 60   150	20   50	20   50	± 60   150	50	3	19	C	963-129
EOC 100K-2XX	<b>(L</b> 60   150	20   50	20   50	± 60   150	100	*2,7	17	D	963-129
EOC 300K-2	150   300	50   100	50   100	± 150   300	100	3	9	В	963-129
EOC 300K-2L	150   300	50   100	50   100	± 150   300	100	3	19	C	963-129
EOC 6K-4A	6	0,5	0,5	± 1,5	2,5	3	6	Α	963-128
EOC 10K-3A	12	1	1	± 3	5	3	7	Α	963-128
EOC 20K-3A	24	2	2	± 6	10	3	6	Α	963-128
EOC 60K-3A	60	5	5	± 15	20	3	7	Α	963-129
EOC 100K-2A	120	10	10	± 30	50	3	9	В	963-129

# **BALANCES & TEST SERVICE 2024**

**KERN Pictograms** 





#### Internal adjusting

Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)



# Adjusting program CAL

For quick setting up of the balance's accuracy. External adjusting weight required



#### **EasyTouch**

Suitable for the connection, data transmission and control through PC or tablet



#### Memory

Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.



#### Alibi memory

Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.



#### **KERN Universal Port** (KUP)

allows the connection of external KUP interface adapters, e.g. RS-232, RS-485, SB, Bluetooth, WIFI, Analogue, Ethernet etc. for the exchange of data and control commands, without installation effort



# RS-232 Data interface

To connect the balance to a printer, PC or network



#### **RS-485 Data interface**

To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible



# **USB** Data interface

To connect the balance to a printer, PC or other peripherals



#### Bluetooth\* Data interface

To transfer data from the balance to a printer, PC or other peripherals



# WIFI Data interface

To transfer data from the balance to a printer, PC or other peripherals



### **Control outputs**

(optocoupler, digital I/O) To connect relays, signal lamps, valves, etc.



#### Analogue interface

to connect a suitable peripheral device for analogue processing of the measurements



#### Interface for second balance

For direct connection of a second balance



#### **Network interface**

For connecting the scale to an Ethernet network



#### **KERN Communication** Protocol (KCP)

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



### GLP/ISO log intern

The balance displays weight, date and time, independent of a printer connection



#### **GLP/ISO log Printer**

With weight, date and time. Only with KERN printers.



#### Piece counting

Reference quantities selectable. Display can be switched from piece to weight



#### Recipe level A

The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out



#### Recipe level B

Internal memory for complete recipés with name and target value of the recipe ingredients. User guidance through display



# Totalising level A

The weights of similar items can be added together and the total can be printed out



Percentage determination Determining the deviation in % from the target value (100 %)



# Weighing units

Can be switched to e.g. nonmetric units. See balance model. Please refer to KERN's website for more details



### Weighing with tolerance range (Checkweighing)

Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model



#### Hold function

(Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value



### Protection against dust and water splashes IPxx

The type of protection is shown in the pictogram

Suspended weighing

Load support with hook



#### on the underside of the balance

**Battery operation** Ready for battery opera-

tion. The battery type is



BATT

# specified for each device

Rechargeable battery pack Rechargeable set



#### Universal plug-in power supply

with universal input and optional input socket adapters for A) EU, CH, GB B) EU, CH, GB, US C) EU, CH, GB, US, AUS



230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available

Plug-in power supply



#### Integrated power supply unit

Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request



#### Weighing principle Strain gauges

Electrical resistor on an elastic deforming body



#### Weighing principle Tuning fork

A resonating body is electromagnetically excited, causing it to oscillate



# Weighing principle Electromagnetic force compensation

Coil inside a permanent magnet. For the most accurate weighings



#### Weighing principle Single cell technology

Advanced version of the force compensation principle with the highest level of precision

M

#### Conformity Assessment

The time required for conformity assessment is specified in the pictogram



#### **DAkkS** calibration possible (DKD)

. The time required for DAkkS calibration is shown in days in the pictogram



#### Factory calibration (ISO)

The time required for Factory calibration is shown in days in the pictogram



#### Package shipment

The time required for internal shipping preparations is shown in days in the pictogram



#### Pallet shipment

The time required for internal shipping preparations is shown in days in the pictogram



<sup>\*</sup>The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners