

Digital Concrete Tester SAUTER FC 1K-BT









Compact force measuring instrument

Features

- Checking the consistency of sprayed concrete is essential to ensure the maximum strength of the concrete during the curing process
- The FC 1K-BT determines exactly the forces required for the needle to penetrate the concrete. This allows reliable conclusions to be made regarding the compressive strength of the concrete during the dry phase
- · Peak-Hold function to capture the peak value or Track function for continuous display of measurement
- · Metal housing for durable use in harsh environmental conditions
- · Capacity display: A bar lights up to show how much of the measuring range is still available
- · Limit value function, programming of Max./ Min., with output of acoustic and optical signal per
- Safety: If loads exceed 110 % of the measuring range, the device will give clear acoustic and
- Internal memory for up to 500 measurement values

- 2 Delivered in a robust carrying case
- · Turnable display with backlight
- Selectable: AUTO-OFF function or continuous operation, charge indicator

Technical data

- Transmission rate to PC: up to 200 measured values/second
- Measuring precision: 0,3 % of [Max]
- Overload protection: 15 0% of [Max]
- Housing dimensions W×D×H 145×73×34 mm
- · Net weight approx. 1,8 kg
- · Selectable measuring units: N, kgf, ozf, lbf
- Robust, cleanable and portable construction
- Built-in 1000 N force measuring cell
- Rapid and simple changing of the penetration needle
- Inverted display for better readability
- Live peak force value for immediate monitoring
- Measurement precision ± 0,1 %
- USB interface

- I Penetration needle and adapter
- Removable if necessary
- Needle diameter: 3 mm
- Upper angle: 60 degrees
- Length: 15 mm
- Included: 15 needles

Accessories

- · Spare needles (set of 15 pieces) for concrete tester SAUTER BT-A01
- · Further accessories see internet and page 39 et seqq.

























Model	Measuring range	Readability	Option DAkkS Calibration Certificate	
			Tensile force	Compressive force
	[Max]	[d]	DAkkS	DAkkS
SAUTER	N	N	KERN	KERN
FC 1K-BT	1000	1	963-162	963-262

MEASURING TECHNOLOGY & TEST SERVICE 2024

SAUTER Pictograms



Conformity assessment

Models with type approval

DAkkS calibration

The time required for

DAkkS calibration is shown

Factory calibration (ISO)

The time required for factory

calibration is specified in

Package shipment

The time required for

internal shipping prepara-

tions is shown in days in

the pictogram

the pictogram

the pictogram

Pallet shipment

The time required for

internal shipping prepara-

tions is shown in days in

in days in the pictogram

systems

possible

for construction of verifiable

M

DAkkS

+3 DAYS

ISO

1 DAY



Adjusting program (CAL)

For quick setting of the instrument's accuracy. External adjusting weight required



Calibration block

Standard for adjusting or correcting the measuring



Peak hold function

Capturing a peak value within a measuring process



Scan mode

Continuous capture and display of measurements



Push and Pull

The measuring device can capture tension and compression forces



Length measurement

Captures the geometric dimensions of a test object or the movement during a test process



Focus function

Increases the measuring accuracy of a device within a defined measuring range



Internal memory

To save measurements in the device memory



Data interface RS-232

Bidirectional, for connection of printer and PC



Profibus

For transmitting data, e.g. between scales, measuring cells, controllers and peripheral devices over long distances. Suitable for safe, fast, fault-tolerant data transmission. Less susceptible to magnetic interference



Profinet

Enables efficient data exchange between de-centralised peripheral devices (balances, measuring cells, measuring instruments etc.) and a control unit (controller). Especially advantageous when exchanging complex measured values, device, diagnostic and process information. Savings potential through shorter commissioning times and device integration possible



Data interface USB

To connect the measuring instrument to a printer, PC or other peripheral devices



Bluetooth* data interface

To transfer data from the balance/measuring instrument to a printer, PC or other peripherals



WIFI data interface

To transfer data from the balance/measuring instrument to a printer, PC or other peripherals



Data interface infrared

To transfer data from the measuring instrument to a printer, PC or other peripheral devices



Control outputs (optocoupler, digital I/O) To connect relays, signal

lamps, valves, etc.



Analogue interface

To connect a suitable peripheral device for analogue processing of the measurements



Analogue output

For output of an electrical signal depending on the load (e.g. voltage 0 V - 10 V or current 4 mA - 20 mA)



Statistics

Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software

To transfer the measurement data from the device to a PC



Printer

A printer can be connected to the device to print out the measurement data



Network interface

For connecting the scale/ measuring instrument to an Ethernet network



KERN Communication Protocol (KCP)

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO record keeping

of measurement data with date, time and serial number. Only with SAUTER printers



Measuring units

Weighing units can be switched to e.g. non-metric. Please refer to website for more details



Measuring with tolerance range (limit-setting function)

Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model



Protection against dust and water splashes IPxx

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989 +A1:1999+A2:2013



ZERO

Resets the display to "0"



Battery operation

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack

Rechargeable set



Plug-in power supply 230V/50Hz in standard

version for EU. On request GB, AUS or US version available



Integrated power supply unit

Integrated, 230V/50Hz in EU. More standards e.g. GB, AUS or US on request



Motorised drive

The mechanical movement is carried out by a electric motor



Motorised drive

The mechanical movement is carried out by a synchronous motor (stepper)



Fast-Move

The total length of travel can be covered by a single lever movement



The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license Other trademarks and trade names are those of their respective owners