

KERN FFN 6K2IPM

All-round bench scale, protected by stainless steel and IP65 rating, verification optional



Accuracy classe	III
Verification scale interval [e]	0,002 kg
Conformity assessment possible ex works	✓

Display	
Display type	LCD
Display backlight	✓
Display digit height	25 mm

Construction	
Dimension housing (W×D×H)	243×300×127 mm
Dimensions completely mounted (W×D×H)	243×300×127 mm
Material housing	stainless steel, plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	233×193 mm
Load cells - number	1
Levelling feet adjustable	✓

Functions	
Number of keys for operation	3
Auto-off interval(s) in mains power mode	3 min
	off
	5 min
Auto-off interval(s) in battery mode/rechargeable battery mode	15 min
	3 min
	off
Tare function	5 min
	15 min
Tare function	manual (single & multi)
Underfloor weighing	None
IP protection - complete device	IP65

Power Supply	
Input voltage power supply / power [Max]	110 V - 230 V AC
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Accu & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK

Category	
Brand	KERN
Product category	Industrial scale
Product group	IP protected bench scale
Product family	FFN

Measuring System	
Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	6 kg
Readability [d]	0,002 kg
Resolution	3.000
Linearity	± 0,002 kg
Reproducibility	0,002 kg
Tare range	-5,998 kg
Default unit	kg
Units	kg
	g
Units (if device is conformity assessed)	kg
	g
Minimum weight [Min]	0,04 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6 kg (M3)
Possible calibration points	3 kg; 6 kg
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,002 kg

Approval	
CE mark	✓

KERN FFN 6K2IPM

KERN

All-round bench scale, protected by stainless steel and IP65 rating, verification optional

Pictograms

STANDARD



OPTION



FACTORY



	US	CH
Rechargeable battery charging time	12 h	
Rechargeable battery operating time - backlight on	30 h	
Rechargeable battery operating time - backlight off	50 h	
Battery	no battery	
Battery / accumulator type	Pb	
Battery connection	Plug-in terminals	

Environmental conditions

Humidity of environment [Min]	25 %
Humidity of environment [Max]	95 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	310×402×205 mm
Net weight	3,85 kg
Shipping method	Parcel service
Net weight approx.	4,0 kg
Gross weight approx.	4,6 kg
Shipping weight	5,1 kg

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for conformity assessment	965-228
Article number for DAKkS calibration	963-128
Article number for certificate of conformity (verification)	969-517