

# KERN HCN 100K200IP

**KERN**

Robust, compact hanging scale with high level of protection against dust and water spray



## Category

Brand	KERN
Product category	Industrial scale
Product group	Hanging scale
Product family	HCN

## Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	100 kg
Readability [d]	0,2 kg
Resolution	500
Linearity	± 0,4 kg
Reproducibility	0,2 kg
Default unit	kg
Units	kg lb N
Adjustment options	Adjusting with external weight
Recommended adjusting weight	50 kg (M3)
Stabilization time	2 s
Warm-up time	10 min
Eccentric/Off-centre loading is not possible	✓
Maximum creep (15 minutes)	400 g
Maximum creep (30 minutes)	800 g
Tolerance (% of [Max])	0,5%
Internal measuring frequency	5 Hz

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD
Display digit height	12 mm

## Construction

Dimension housing (W×D×H)	96×48×179 mm
Material housing	stainless steel
Material load hook	stainless steel
Material load cell(s)	Stainless steels

## Functions

Number of keys for operation	3
Auto-off interval(s) in mains power mode	3 min
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Hold function	✓
Underfloor weighing	None
IP protection - complete device	IP65

## Power Supply

Supplied power supply	Battery
Battery	2×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery voltage	3 V
Battery operating time	200 h

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Max]	60 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	150×220×73 mm
Net weight	0,452 kg
Shipping method	Parcel service
Net weight approx.	0,50 kg
Gross weight approx.	1,2 kg
Shipping weight	1,1 kg

## Services (optional)

Article number for adjustment at the location of installation	961-249
---	---------

# KERN HCN 100K200IP



Robust, compact hanging scale with high level of protection against dust and water spray

Article number for DAkkS calibration 963-129H

Article number for certificate of conformity (verification) 969-517

## Pictograms

### STANDARD



### OPTION

