

# KERN IOC 300K-2M

# KERN

Allround platform scale with a wide range of communication options, verification optional



Accuracy classe	III
Verification scale interval [e]	0,05 kg; 0,1 kg
Conformity assessment possible ex works	✓

## Display

Display type	LCD
Display type	LCD
Display screen size	110×35 mm
Display backlight	✓
Display digit height - smallest digit	25 mm
Display digit height	25 mm
Languages of the user interface	Symbol language

## Construction

Dimension display device (W×D×H)	268×115×80 mm
Dimensions weighing platform (W×D×H)	650×500×150 mm
Material display housing	Plastics
Material weighing plate	stainless steel
Material platform	mild steel
Dimensions weighing surface (W×D)	650×500 mm
Display device cable length	3 m
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Wall mount	✓
Stand inclinable	✓

## Functions

Number of keys for operation	7
Auto-off interval(s) in mains power mode	3 min off 5 min 30 min 15 min
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 30 min 15 min
PreTare function	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual

## Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IOC

## Measuring System

Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	150 kg; 300 kg
Readability [d]	0,05 kg; 0,1 kg
Resolution	3.000, 3.000
Linearity	± 0,05 kg; 0,1 kg
Linearisation in dots	3
Reproducibility	0,05 kg; 0,1 kg
Tare range	-300 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	1 kg; 2 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	300 kg (M1)
Stabilization time	2 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,05 kg; 0,1 kg
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	6-wire

## Approval

CE mark	✓
---------	---

# KERN IOC 300K-2M



Allround platform scale with a wide range of communication options, verification optional

Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 standard
	Ethernet (optional, factory)
	USB (optional, factory)
	WiFi (optional, factory)
	Alibi memory (optional, factory)
	USB-Host/Master (optional, factory)
	Verification plug (optional, factory)
Bluetooth BLE (v4.0) (optional, factory)	
IP protection - complete device	IP65
IP protection - display	IP65
IP protection - load cell	IP65
IP protection - platform	IP65

Counting	
Smallest piece weight when piece counting - laboratory conditions	10 g
Smallest piece weight when piece counting - normal conditions	100 g
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	30.000

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0.4 A max
Input voltage device / power [Max]	12 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK US
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	3 h

Rechargeable battery operating time - backlight on	26 h
Rechargeable battery operating time - backlight off	43 h
Battery / accumulator type	Pb
Battery operating time	100 h

Environmental conditions	
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	1050×740×175 mm
Net weight	21,9 kg
Shipping method	Parcel service
Net weight approx.	22 kg
Gross weight approx.	26 kg
Shipping weight	27,2 kg

Services (optional)	
Article number for adjustment at the location of installation	961-249
Article number for conformity assessment	965-229
Article number for DAkKS calibration	963-129
Article number for certificate of conformity (verification)	969-517


# KERN IOC 300K-2M



Allround platform scale with a wide range of communication options, verification optional

## Pictograms

### STANDARD



### OPTION



### FACTORY

