

KERN JCT 100

New-generation measuring coating thickness gauge



Category	
Brand	Sauter
Product category	Coating thickness measuring device
Product group	Digital coating thickness gauge
Product family	JCT
Measuring System	
Units	µm inch (mil)
Tolerance (% of [Max])	2%
Readability coating thickness [d] (µm)	0,1 µm
Minimum thickness coating	300 µm
Measuring range coating thickness [d] (µm)	2000 µm
Sensor placement position	internal
Coating thickness gauge sensor type	FE NFE
Test object thickness coating	Non-magnetic coatings on iron, steel, Type F Coatings on non-magnetic metals, type N
Smallest sample, flat [radius]	10 mm
Smallest sample, concave [radius]	50 mm
Smallest sample, convex [radius]	1,5 mm
Internal data memory: Number of value groups	55
Internal data memory: Number of individual values	60

Approval

CE mark	✓
---------	---

Display

Display type	LCD graphic
Display type	LCD Graphic
Display screen size	2 "
Display resolution	240×320
Screen reversible	✓

Construction

Dimension (W×D×H)	152×65×35 mm
Dimension display device (W×D×H)	152×65×35 mm
Dimension housing (W×D×H)	152×65×35 mm
Dimensions completely mounted (W×D×H)	152×65×35 mm
Material housing	plastic

Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
Hold function	✓
Peak function	✓
Statistic function	✓
Continuous capture possible	✓
Limit-setting function	✓
Memory function	✓
Interfaces	Bluetooth USB 2.0

Power Supply

Supplied power supply	Accu
Plug-in power supply / adapter for countries - optional	EURO
Rechargeable battery charging time	3 h
Rechargeable battery operating time - backlight on	6 h
Rechargeable battery operating time - backlight off	8 h
Battery / accumulator type	Li-Ion
Battery connection	Connector pin
Battery operating time	20 h

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	250×198×50 mm

KERN JCT 100



New-generation measuring coating thickness gauge

Net weight	0,18 kg
Shipping method	Parcel service
Net weight approx.	0,20 kg
Gross weight approx.	0,75 kg
Shipping weight	0,75 kg

Pictograms

STANDARD

