

KERN KFN-TM

Stainless steel display device with IP65 protection and superior display size and optional analogue output for controlling systems (PLC) etc.



| | |
|------------------|-----------------|
| Material housing | stainless steel |
| Wall mount | ✓ |

Functions

| | |
|--|------------------------|
| Number of keys for operation | 7 |
| Auto-off interval(s) in mains power mode | off 5 min 15 min |
| Auto-off interval(s) in battery mode/rechargeable battery mode | off 5 min 15 min |
| Tare function | manual (multi) |
| Hold function | ✓ |
| Counting function | ✓ |
| Tolerance weighing | ✓ |
| Tolerance weighing - type of signal | acoustically visual |
| Function for averaging under unstable weighing conditions | ✓ |
| Conversion function | ✓ |
| Recipe/summing level | Sum A |
| Sum memory function | ✓ |

| | |
|------------|---|
| Interfaces | RS-232 (optional, factory) Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory) |
|------------|---|

| | |
|-------------------------|------|
| IP protection - display | IP65 |
|-------------------------|------|

Counting

| | |
|--------------------|----------------------|
| Reference quantity | 10, 20, 50, 100, 200 |
|--------------------|----------------------|

Power Supply

| | |
|---|------------------------|
| Input voltage power supply / power [Max] | 110 V - 230 V AC |
| Input voltage device / power [Max] | 12 V, 500 mA |
| Plug-in power supply type | Power adapter |
| Supplied power supply | Accu & Power supply |
| Plug-in power supply / adapter for countries - included with the delivery | EURO UK US CH |

| | |
|---|-------------------------------|
| Plug-in power supply / adapter for countries - optional | EURO AUS UK US CH |
|---|-------------------------------|

Category

| | |
|------------------|----------------|
| Brand | KERN |
| Product category | Component |
| Product group | Display device |
| Product family | KFN-TM |

Measuring System

| | |
|--------------------------------------|--------------------------------|
| Number of weighing ranges | 2 |
| Terminal resolution (not verifiable) | 30.000 |
| Terminal resolution (verifiable) | 6.000 |
| Linearisation in dots | 3 |
| Default unit | kg |
| Units | kg |
| Adjustment options | Adjusting with external weight |

Approval

| | |
|---|-----|
| CE mark | ✓ |
| Accuracy classe | III |
| Conformity assessment possible ex works | ✓ |

Display

| | |
|----------------------|--------------------|
| Display type | LCD |
| Display type | LCD with backlight |
| Display backlight | ✓ |
| Display digit height | 52 mm |

Construction

| | |
|----------------------------------|-------------------|
| Dimension display device (W×D×H) | 266×165×96 mm |
| Dimension housing (W×D×H) | 265,5×164,5×96 mm |
| Material display housing | stainless steel |

KERN KFN-TM



Stainless steel display device with IP65 protection and superior display size and optional analogue output for controlling systems (PLC) etc.

| | |
|---|-------------------|
| Rechargeable battery charging time | 12 h |
| Rechargeable battery operating time - backlight on | 20 h |
| Rechargeable battery operating time - backlight off | 35 h |
| Battery / accumulator type | Pb |
| Battery connection | Plug-in terminals |

Environmental conditions

| | |
|---------------------------|--------|
| Ambient temperature [Min] | -10 °C |
| Ambient temperature [Max] | 40 °C |

Packing & Shipping

| | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 330×255×220 mm |
| Net weight | 2,5 kg |
| Shipping method | Parcel service |
| Net weight approx. | 2,6 kg |
| Gross weight approx. | 3,2 kg |
| Shipping weight | 3,7 kg |

Services (optional)

| | |
|---|--------------------------|
| Article number for adjustment at the location of installation | auf Anfrage on request |
|---|--------------------------|

Pictograms

STANDARD



FACTORY

