

# KERN MAP 80K1

# KERN

Hand grip dynamometer, e.g. for rehabilitation treatment after accidents



|                            |          |
|----------------------------|----------|
| Battery / accumulator type | Li-Metal |
| Battery capacity           | 630 mAh  |
| Battery voltage            | 3 V      |
| Battery operating time     | 53 h     |

|                               |        |
|-------------------------------|--------|
| Environmental conditions      |        |
| Use temperature [Min]         | 5 °C   |
| Use temperature [Max]         | 35 °C  |
| Humidity of environment [Max] | 80 %   |
| Storage temperature [Min]     | -20 °C |
| Storage temperature [Max]     | 60 °C  |

|  |                |
|--|----------------|
| Packing & Shipping                     |                |
| Dimensions transport container (W×D×H) | 350×265×85 mm  |
| Readability force [d] (N)              | 1 d            |
| Dimensions packaging (W×D×H)           | 367×285×100 mm |
| Net weight                             | 0,306 kg       |
| Shipping method                        | Parcel service |
| Net weight approx.                     | 0,35 kg        |
| Gross weight approx.                   | 1,8 kg         |
| Shipping weight                        | 2,1 kg         |

|  |          |
|--|----------|
| Services (optional)                    |          |
| Article number for factory calibration | 961-102K |

## Pictograms

### STANDARD



### OPTION



## Category

|                  |                       |
|------------------|-----------------------|
| Brand            | KERN                  |
| Product category | Medical scale         |
| Product group    | Hand grip dynamometer |
| Product family   | MAP                   |

## Measuring System

|                              |            |
|------------------------------|------------|
| Weighing capacity [Max]      | 80 kg      |
| Readability [d]              | 100 g      |
| Units                        | kg<br>lb   |
| Recommended adjusting weight | 40 kg (M1) |
| Possible calibration points  | 40 kg      |

## Approval

|         |   |
|---------|---|
| CE mark | ✓ |
|---------|---|

## Display

|                      |             |
|----------------------|-------------|
| Display type         | LCD graphic |
| Display digit height | 12 mm       |

## Construction

|                           |               |
|---------------------------|---------------|
| Dimensions device (W×D×H) | 55×102×212 mm |
|---------------------------|---------------|

## Functions

|  |       |
|--|-------|
| Auto-off interval(s) in battery mode/rechargeable battery mode | 1 min |
|--|-------|

## Power Supply

|                       |         |
|-----------------------|---------|
| Supplied power supply | Battery |
| Battery               | CR2450  |