

Baby Scale KERN MBD



Ergonomically-optimised baby scale with large lying surface

Features

- Modern design
- Large, ergonomically optimised tray for safe weighing of neonates
- Robust plastic tray
- Easy and hygienic cleaning
- Particularly flat and lightweight construction, so it is easy to transport and store
- Secure and non-slip positioning with rubber feet
- Easy to use
- Hold function: While weighing patients that are unable to lie still, a mean average weight value is determined. This allows for sufficient time to attend to the young patient, and then get a weight reading
- Difference function for calculating the weight gain before and after feeding
- Internal weight memory for one weight value
- Integrated AUTO-OFF function to preserve the batteries
- Weight displayed in kg or lb
- **Note:** The models are only delivered in a set of 5 units. That means the price refers to a delivery of 5 units. Cannot be delivered individually

Technical data

- LCD display, digit height 30 mm
- Dimensions of tray W×D 560×225 mm
- Overall dimensions W×D×H 597×350×74 mm
- Batteries included, 2×1.5 V AAA, operating time up to 20 h
- Net weight approx. 2,0 kg (per piece)

Accessories

- Cleaning cloths, alcohol-free cloths for disinfectant wiping, quick acting, based on modern quaternary ammonium compounds and effective against papova viruses. Particularly gentle on materials, and very well suited for disinfecting products which are sensitive to alcohol. Fulfill the legal requirements for occupational safety in accordance with TRGS 525/540. Packaging contents 100 pcs., size 20×22 cm per cloth, KERN MYC-01
- **1** Carrying bag for mobile use, a carrying handle and shoulder strap ensure comfortable handling. Note: The models are only delivered in a set of 5 units. That means the price refers to a delivery of 5 units. Cannot be delivered individually, KERN YTB-01S05
- **2** Backpack for mobile use, 2 padded carrying straps and carrying handles for safe, convenient handling, additional, large zipped compartment for storing objects. Note: The models are only delivered in a set of 5 units. That means the price refers to a delivery of 5 units. Cannot be delivered individually, KERN YTB-02S05

STANDARD



Model	Weighing capacity	Readability
	[Max]	[d]
KERN	kg	kg
MBD 20K-2S05	15	0,01

CAL EXT
Adjusting program CAL
 For quick setting up of the balance's accuracy. External adjusting weight required

MEMORY
Memory
 Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.

RS 232
Data interface RS-232
 To connect the balance to a printer, PC or network

RS 485
RS-485 data interface
 To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible

USB
USB data interface
 To connect the balance to a printer, PC or other peripherals

BT
Bluetooth* data interface
 To transfer data from the balance to a printer, PC or other peripherals

WIFI
WIFI data interface
 To transfer data from the balance to a printer, PC or other peripherals

SWITCH
Control outputs (optocoupler, digital I/O)
 To connect relays, signal lamps, valves, etc.

STATISTIC
Statistics
 Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.

SOFTWARE
PC Software
 to transfer the measurements from the device to a PC

GLP INTERN
GLP/ISO log internal
 The balance displays weight, date and time, independent

GLP PRINTER
GLP/ISO log
 With date and time. Only with KERN printers

KCP PROTOCOL
KERN Communication Protocol (KCP)
 It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems

PCS
Piece counting
 Reference quantities selectable. Display can be switched from piece to weight

SUM
Totalising level A
 The weights of similar items can be added together and the total can be printed out

UNIT
Weighing units
 Can be switched to e.g. nonmetric units. Please refer to website for more details

TOL
Weighing with tolerance range (Check weighing)
 Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model

ZERO
ZERO
 Resets the display to "0"

MOVE
Hold function
 When patients do not stand, sit or lie completely still, a stable weight is calculated using an average weight

MOVE
Hold function
 When the weighing conditions are unstable, a stable weight is calculated as an average value

IP
Protection against dust and water splashes IPxx
 The type of protection is shown in the pictogram of. DIN EN 60529:2000-09, IEC0529:1989+A1:1999 +A2:2013

UNDER
Suspended weighing
 Load support with hook on the underside of the balance

BATT
Battery operation
 Ready for battery operation. The battery type is specified for each device

RECHARGE
Battery operation rechargeable
 Prepared for a rechargeable battery operation

ACCU
Rechargeable battery pack
 Rechargeable set

MULTI
Universal plug-in power supply
 with universal input and optional input socket adapters for
 A) EU, CH
 B) EU, CH, GB, US
 C) EU, CH, GB, US, AUS

230 V
Plug-in power supply
 230V/50Hz in standard version for EU. On request GB, AUS or US version available

230 V
Integrated power supply unit
 Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, AUS or US on request

DMS
Weighing principle Strain gauges
 Electrical resistor on an elastic deforming body

PEAK
Peak hold function
 capturing a peak value within a measuring process

PUSH/PULL
Push and Pull
 the measuring device can capture tension and compression forces

SCALE
Integrated scale
 In the eyepiece

360°
360° rotatable microscope head

360°
Monocular Microscope
 For the inspection with one eye

BINDO
Binocular Microscope
 For the inspection with both eyes

TRINO
Trinocular Microscope
 For the inspection with both eyes and the additional option for the connection of a camera

ABBE
Abbe Condenser
 With high numerical aperture for the concentration and the focusing of light

HAL
Halogen illumination
 For pictures bright and rich in contrast

LED
LED illumination
 Cold, energy-saving and especially long-life illumination

FL-HBD
Fluorescence illumination for compound microscopes
 With 100 W mercury lamp and filter

FL-LED
Fluorescence illumination for compound microscopes
 With 3 W LED illumination and filter

PH
Phase contrast unit
 For a higher contrast

DF
Darkfield condenser/unit
 For a higher contrast due to indirect illumination

POLAR
Polarising unit
 To polarise the light

INFINITY
Infinity system
 Infinity corrected optical system

AUTO ATC
Automatic temperature compensation
 For measurements between 10 °C and 30 °C

M +3 DAYS
Conformity assessment
 The time required for conformity assessment is specified in the pictogram

1 DAY
Package shipment
 The time required for internal shipping preparations is shown in days in the pictogram

2 DAYS
Pallet shipment
 The time required for internal shipping preparations is shown in days in the pictogram

*The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.