

# KERN PCD 6K-4

# KERN

High-resolution precision balance with removable display for maximum flexibility



Eccentric loading at 1/3 [Max]	0,5 g
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD
Display backlight	✓
Display digit height	21 mm
Languages of the user interface	English

## Construction

Dimensions device (W×D×H)	165×280×75 mm
Dimension display device (W×D×H)	140×46×75 mm
Dimension housing (W×D×H)	165×280×75 mm
Dimensions weighing platform (W×D×H)	161×161×7 mm
Dimensions completely mounted (W×D×H)	165×280×75 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	160×160 mm
Display device cable length	1,2 m
Levelling feet adjustable	✓
Stand height	250 mm
Stand inclinable	✓

## Functions

Number of keys for operation	5
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Peak function	✓
Recipe/summing level	Rez A (Net total)
Underfloor weighing	None
Interfaces	RS-232 standard

## Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PCD

## Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	6000 g
Readability [d]	0,1 g
Resolution	60.000
Linearity	± 0,3 g
Reproducibility	0,1 g
Tare range	6000 g
Default unit	g

Units	g
	gn
	dwt
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
	oz
	ffa
tol	

USP Minimum weight of sample (k = 2, U = 0.1%)	200 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6 kg (F1)
Stabilization time	3 s
Warm-up time	120 min

# KERN PCD 6K-4

High-resolution precision balance with removable display for maximum flexibility

## Counting

Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Reference quantity	5, 10, 20, 25, 50
Counting resolution (laboratory conditions)	30.000

## Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	9 V, 300 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	US
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	10 h
Rechargeable battery operating time - backlight on	12 h
Rechargeable battery operating time - backlight off	24 h
Battery	9 V block
Battery connection	Plug-in terminals
Battery operating time	12 h

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	250×360×160 mm
Net weight	1,7 kg
Shipping method	Parcel service
Net weight approx.	1,8 kg
Gross weight approx.	2,2 kg
Shipping weight	2,9 kg

## Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION

