

KERN PNJ 600-3M

KERN

The new standard in the laboratory with robust tuning fork weighing system



USP Minimum weight of sample (k = 2, U = 0.1%)	2 g
Minimum weight [Min] (ct)	0,2 ct
Adjustment options	Internal calibration (automatic)
Stabilization time	3 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,004 g

Approval	
CE mark	✓
Accuracy classe	II
Verification scale interval [e]	0,01 g
Verification scale interval [e] (ct)	0,1 ct
Conformity assessment possible ex works	✓

Display	
Display type	LCD
Display type	LCD
Display screen size	109×27 mm
Display backlight	✓
Display digit height	16,5 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	196×293×266 mm
Dimensions rectangular draught shield - inner (W×D×H)	172×171×160 mm
Dimensions completely mounted (W×D×H)	196×293×266 mm
Material housing	plastic
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	140 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	5
Capacity - Display	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Interfaces	RS-232 standard
IP protection - display	no IP protection
IP protection - platform	no IP protection

Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PNJ

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Tuning fork
Weighing capacity [Max]	620 g
Weighing capacity [Max] (ct)	3100 ct
Readability [d]	0,001 g
Readability carat [d] (ct)	0,01 ct
Resolution	620.000
Linearity	± 0,004 g
Reproducibility	0,001 g
Tare range	620 g
Default unit	g

	g
	gn
	dwt
	tl (Tw)
	tl (HK)
Units	ozt
	tl (Singap, Malays)
	ct
	mo
	lb
	oz
	tol

Units (if device is conformity assessed)	g
	ct

Minimum weight [Min]	0,02 g
----------------------	--------

KERN PNJ 600-3M



The new standard in the laboratory with robust tuning fork weighing system

Counting

Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Counting reference weight can be entered	✓
Reference quantity	10, 30, 50, 100
Counting resolution (laboratory conditions)	620.000

Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	5,95 V, 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
	EURO
Plug-in power supply / adapter for countries - included with the delivery	AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (WxDxH)	409×320×318 mm
Net weight	4,17 kg
Shipping method	Parcel service
Net weight approx.	4,2 kg
Gross weight approx.	6 kg
Shipping weight	8,3 kg

Services (optional)

Article number for conformity assessment	965-216
Article number for DAkkS calibration	963-103
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

