

# KERN SP 200K

# KERN

Compact photometer, optimised for accurate light measurement, including LED light measurement



## Category

Brand	Sauter
Product category	Environment/ Occupational safety
Product group	Light measuring instrument
Product family	SP

## Measuring System

Units	lx fc
Measuring head measuring frequency	2 Hz
Measuring range [Max] (Lux)	200 lx; 2000 lx; 20000 lx; 200000 lx
Readability illumination [d] (lx)	0,1 lx; 1 lx; 10 lx; 100 lx

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD
Display digit height	16 mm

## Construction

Dimension housing (W×D×H)	185×68×38 mm
Dimensions completely mounted (W×D×H)	185×68×38 mm
Material display housing	Plastics
Material housing	plastic

## Functions

Hold function	✓
Peak function	✓

## Power Supply

Supplied power supply	Battery
Battery	9 V block
Battery / accumulator type	Alkali(-Manganese)
Battery connection	9V Bloc
Battery voltage	9 V
Battery operating time	200 h

## Environmental conditions

Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	200×106×55 mm
Net weight	0,13 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,30 kg
Shipping weight	0,28 kg

## Services (optional)

Article number for factory calibration	961-190
---	---------

## Pictograms

### STANDARD



### OPTION

