


KERN ALS 160-4A

KERN

Analytical balance with high weighing capacity, graphic display and convenient recipe function



Possible calibration points	100 g; 150 g
Stabilization time	4 s
Warm-up time	8 h
Eccentric loading at 1/3 [Max]	0,0004 g
Maximum creep (15 minutes)	1 mg
Maximum creep (30 minutes)	2 mg

Approval

CE mark	✓
---------	---

Display

Display type	LCD graphic
Display screen size	132×38 mm
Display backlight	✓
Display digit height - smallest digit	4 mm
Display digit height	15 mm
Languages of the user interface	English

Construction

Dimension housing (W×D×H)	210×340×330 mm
Dimensions rectangular draught shield - inner (W×D×H)	160×170×225 mm
Dimensions rectangular draught shield - outer (W×D×H)	172×185×245 mm
Dimensions completely mounted (W×D×H)	210×340×330 mm
Material housing	plastic
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	80 mm
Transport safety lock - bolt torque	0,1 Nm
Levelling feet adjustable	✓

Functions

Number of keys for operation	6
Auto-off interval(s) in mains power mode	off 5 min 2 min 15 min
Capacity - Display	✓
PreTare function	✓
Tare function	manual (multi)
Density determination	✓
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual

Category

Brand	KERN
Product category	Laboratory balance
Product group	Analytical balance
Product family	ALS-A

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Force compensation
Weighing capacity [Max]	160 g
Weighing capacity [Max] (ct)	800 ct
Readability [d]	0,0001 g
Readability carat [d] (ct)	0,001 ct
Resolution	1.600.000
Linearity	± 0,0003 g
Reproducibility	0,0001 g
Default unit	g

Units	g
	mg
	gn
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
lb	
oz	

USP Minimum weight of sample (k = 2, U = 0.1%) 200 mg

Adjustment options Adjusting with external weight

Recommended adjusting weight 150 g (E2)

KERN ALS 160-4A



Analytical balance with high weighing capacity, graphic display and convenient recipe function

Function for averaging under unstable weighing conditions	✓
Standby function	✓
Recipe/summing level	Rez B (Net-total, memory with plain text designations + setpoint, also for printout)
Recipe weighing - number of database entries	99
Recipe weighing - number of ingredients per database entry	20
Underfloor weighing	None
Interfaces	RS-232 standard

Counting

Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Counting reference weight can be entered	✓
Reference quantity	10, 25, 50, 100, n (any number of pieces)
Counting resolution (laboratory conditions)	160.000

Power Supply

Input voltage power supply / power [Max]	country dependent
Input voltage device / power [Max]	24 V 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
---------------------------	-----


Dimensions packaging (W×D×H)	400×515×615 mm
Net weight	6,2 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	9 kg
Shipping weight	25,3 kg

Services (optional)

Article number for DAkkS calibration	963-101
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

