


# KERN BFN 1.5T0.5M

Stainless steel weighing bridge with screwed-on weighing plate (IP68) and stainless steel display device (IP65), verification optional



Accuracy classe	III
Verification scale interval [e]	0,5 kg
Conformity assessment possible ex works	✓

## Display

Display type	LCD
Display type	LCD with backlight
Display screen size	165×64 mm
Display backlight	✓
Display digit height	52 mm
Languages of the user interface	Symbol language

## Construction

Dimension display device (W×D×H)	266×165×96 mm
Dimensions weighing platform (W×D×H)	1500×1250×85 mm
Dimensions completely mounted (W×D×H)	1495×1245×95 mm
Material display housing	stainless steel
Material weighing plate	stainless steel
Material platform	stainless steel (SUS304)
Dimensions weighing surface (W×D)	1500×1250 mm
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	30 m
Material load cell(s)	Stainless steels
Load cells - number	4
Levelling feet adjustable	✓
Wall mount	✓
Stand inclinable	✓

## Functions

Number of keys for operation	7
Auto-off interval(s) in mains power mode	3 min off 5 min 30 min 15 min
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 30 min 15 min
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓

## Category

Brand	KERN
Product category	Industrial scale
Product group	Floor scale
Product family	BFN

## Measuring System

Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	1500 kg
Readability [d]	0,5 kg
Resolution	3.000
Linearity	± 1,5 kg
Reproducibility	0,5 kg
Tare range	-1500 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Minimum weight [Min]	10 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	1500 kg (M1)
Stabilization time	2 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	2,5 kg
Loadcell type	ZEMIC BM8H 1 ton
Load cell connection	4-wire

## Approval

CE mark	✓
---------	---

# KERN BFN 1.5T0.5M

Stainless steel weighing bridge with screwed-on weighing plate (IP68) and stainless steel display device (IP65), verification optional

Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Sum memory function	✓
Interfaces	RS-232 (optional, factory) Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
IP protection - complete device	-
IP protection - display	IP65
IP protection - load cell	IP68
IP protection - platform	IP67

Counting	
Reference quantity	10, 20, 50, 100, 200

Power Supply	
Input voltage power supply / power [Max]	110 V - 230 V AC
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Accu & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH

Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
---	-------------------------------

Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	35 h
Battery	no battery
Battery / accumulator type	Pb
Battery connection	Plug-in terminals

Environmental conditions	
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %


Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping	
Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	1270×1510×345 mm
Net weight	120 kg
Shipping method	Freight
Net weight approx.	120 kg
Gross weight approx.	185 kg
Shipping weight	185 kg

Services (optional)	
Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION



### FACTORY

