


KERN CCA 60K-4M

High-resolution counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999, verification optional



Display

Display type	LCD
Display backlight	✓
Display digit height	20 mm

Construction

Dimension display device (W×D×H)	250×160×65 mm
Dimensions weighing platform (W×D×H)	400×300×120 mm
Material housing	plastic
Material weighing plate	coated metal
Material platform	Stainless steel
Dimensions weighing surface (W×D)	400×300 mm
Cable length	1,5 m
Display device cable length	5 m
Material load cell(s)	aluminium
Levelling feet adjustable	✓

Functions

Number of keys for operation	28
PreTare function	✓
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Conversion function	✓
Recipe/summing level	Rez A (Net total)
PLU - total	100
Sum memory function	✓
Memory function	✓
Interfaces	RS-232 standard
IP protection - complete device	IP23
IP protection - display	no IP protection
IP protection - load cell	IP65
IP protection - platform	IP65

Counting

Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, 100

Category

Brand	KERN
Product category	Industrial scale
Product group	Counting system
Product family	CCA

Measuring System

Reference scale - item number	EWJ 6000-1M
Quantity scale - Item number	IFS 60K-2M
Weighing system	Strain gauge
Reference scale - Weighing capacity [Max]	6 kg
Quantity scale - Weighing capacity [Max]	30 kg; 60 kg
Reference scale - Readability [d]	100 mg
Quantity scale - Readability [d]	0,01 kg; 0,02 kg
Linearity	±
Reference scale - Linearity	300 mg
Quantity scale - Linearity	0,01 kg; 0,02 kg
Reference scale - Reproducibility	100 mg
Quantity scale - Reproducibility	0,01 kg; 0,02 kg
Default unit	kg
Units	kg
Units (if device is conformity assessed)	kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	6 kg (M1)
Stabilization time	2 s
Reference scale - Eccentric loading at 1/3 [Max]	300 mg
Quantity scale - Eccentric loading at 1/3 [Max]	0,01 kg; 0,02 kg

Approval

CE mark	✓
Conformity assessment possible ex works	✓

KERN CCA 60K-4M



High-resolution counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999, verification optional

Counting resolution (laboratory conditions)	600.000
---	---------

Power Supply

Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	18 h
Battery	no battery
Battery / accumulator type	Pb
Battery connection	Plug-in terminals

Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping


Readability force [d] (N)	4 d
Dimensions packaging (WxDxH)	795x460x490 mm
Net weight	13,5 kg
Shipping method	Parcel service
Net weight approx.	14 kg
Gross weight approx.	17 kg
Shipping weight	35,8 kg

Services (optional)

Article number for conformity assessment	965-229-216
Article number for DAkkS calibration	962-129-127
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

