


# KERN CCS 3T-3L

Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999



## Approval

CE mark	✓
---------	---

## Display

Display type	LCD
Display backlight	✓
Display digit height	20 mm

## Construction

Dimension housing (W×D×H)	320×350×125 mm
Dimensions weighing platform (W×D×H)	1500×1500×108 mm
Material housing	plastic
Material weighing plate	coated metal
Dimensions weighing surface (W×D)	1500×1500 mm
Cable length	1,5 m
Display device cable length	5 m
Material load cell(s)	aluminium
Levelling feet adjustable	✓

## Functions

Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
PreTare function	✓
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Conversion function	✓
Recipe/summing level	Rez A (Net total)
PLU - total	100
Sum memory function	✓
Memory function	✓
Interfaces	RS-232 standard
IP protection - display	IP23
IP protection - load cell	IP65
IP protection - platform	IP65

## Counting

Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)

## Category

Brand	KERN
Product category	Industrial scale
Product group	Counting system
Product family	CCS

## Measuring System

Reference scale - item number	CFS 6K0.1
Quantity scale - Item number	KIP 3000V20LM
Weighing system	Strain gauge
Reference scale - Weighing capacity [Max]	6 kg
Quantity scale - Weighing capacity [Max]	3000 kg
Reference scale - Readability [d]	100 mg
Quantity scale - Readability [d]	1 kg
Linearity	±
Reference scale - Linearity	200 mg
Quantity scale - Linearity	2 kg
Reproducibility	0,0002 kg
Reference scale - Reproducibility	100 mg
Quantity scale - Reproducibility	1 kg
Default unit	kg
Units	kg lb
Adjustment options	Adjusting with external weight
Recommended adjusting weight	3000 kg (M1)
Stabilization time	2 s
Eccentric loading at 1/3 [Max]	0,0005 kg
Reference scale - Eccentric loading at 1/3 [Max]	500 mg
Quantity scale - Eccentric loading at 1/3 [Max]	2 kg

# KERN CCS 3T-3L



Counting system to count the smallest parts in large quantities, maximum number of parts which can be displayed is 999,999

Counting resolution (laboratory conditions)	30.000.000
---	------------

## Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO CH
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	70 h
Rechargeable battery operating time - backlight off	60 h
Battery / accumulator type	Pb

## Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

## Packing & Shipping

Readability force [d] (N)	4 d
Dimensions packaging (W×D×H)	1550×1550×265 mm
Net weight	110 kg
Shipping method	Freight
Net weight approx.	110 kg
Gross weight approx.	115 kg
Shipping weight	115 kg

## Services (optional)

Article number for adjustment at the location of installation	abhängig von Auflösung/ Max   depends on resolution and capacity
Article number for DAkkS calibration	962-132-128
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION

