

KERN CDS 15K0.05

Easy to use industrial counting scale for heavy loads, counting resolution 300.000 points, ideal for the diverse possibilities of Industry 4.0 applications



| | |
|----------------------------|--------|
| Maximum creep (15 minutes) | 500 mg |
| Maximum creep (30 minutes) | 1 g |

Approval

| | |
|---------|---|
| CE mark | ✓ |
|---------|---|

Display

| | |
|---------------------------------|----------------------------|
| Display type | LCD |
| Display type | 7 segment LED |
| Display screen size | 89×30 mm |
| Display backlight | ✓ |
| Display digit height | 21 mm |
| Languages of the user interface | English Symbol language |

Construction

| | |
|--------------------------------------|------------------|
| Dimension display device (W×D×H) | 225×115×60 mm |
| Dimension housing (W×D×H) | 225×115×60 mm |
| Dimensions weighing platform (W×D×H) | 308×318×75 mm |
| Material display housing | Plastics |
| Material housing | plastic |
| Material weighing plate | stainless steel |
| Material platform | metal, lacquered |
| Dimensions weighing surface (W×D) | 308×318 mm |
| Display device cable length | 2,5 m |
| Wall mount | ✓ |

Functions

| | |
|--|---|
| Number of keys for operation | 7 |
| Auto-off interval(s) in mains power mode | off |
| Auto-off interval(s) in battery mode/rechargeable battery mode | 5 min 2 min 1 min 30 min 60 min 30 sec |
| PreTare function | ✓ |
| Tare function | manual (multi) |
| Percentage determination | ✓ |
| Counting function | ✓ |
| Tolerance weighing | ✓ |
| Tolerance weighing - type of signal | acoustically visual |
| Function for averaging under unstable weighing conditions | ✓ |

Category

| | |
|------------------|------------------|
| Brand | KERN |
| Product category | Industrial scale |
| Product group | Counting scale |
| Product family | CDS |

Measuring System

| | |
|--------------------------------|----------------------|
| Construction type of the scale | Single-range balance |
| Weighing system | Strain gauge |
| Weighing capacity [Max] | 15 kg |
| Readability [d] | 0,00005 kg |
| Resolution | 300.000 |
| Linearity | ± 0,00025 kg |
| Reproducibility | 0,0001 kg |
| Default unit | kg |

| | |
|-------|---|
| Units | kg g dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa |
|-------|---|

| | |
|--------------------------------|--------------------------------|
| Adjustment options | Adjusting with external weight |
| Recommended adjusting weight | 15 kg (F1) |
| Possible calibration points | 2 kg; 5 kg; 10 kg; 15 kg |
| Stabilization time | 3 s |
| Warm-up time | 120 min |
| Eccentric loading at 1/3 [Max] | 0,00025 kg |

KERN CDS 15K0.05



Easy to use industrial counting scale for heavy loads, counting resolution 300.000 points, ideal for the diverse possibilities of Industry 4.0 applications

| | |
|---------------------|-----------------------|
| Underfloor weighing | Hook (optional) |
| | RS-232 (optional) |
| | Ethernet (optional) |
| | Bluetooth BLE (v4.0) |
| Interfaces | (optional) |
| | USB-Device (optional) |
| | KUP |
| | WiFi (optional) |

| Counting | |
|---|---|
| Smallest piece weight when piece counting - laboratory conditions | 50 mg |
| Smallest piece weight when piece counting - normal conditions | 500 mg |
| Counting reference weight can be entered | ✓ |
| Reference quantity | 5, 10, 20, 50, n (any number of pieces) |
| Counting resolution (laboratory conditions) | 300.000 |

| Power Supply | |
|---|------------------------------|
| Input voltage power supply / power [Max] | 100 V - 240 V AC, 50 / 60 Hz |
| Input voltage device / power [Max] | 5,9V, 1A |
| Plug-in power supply type | Power adapter |
| Supplied power supply | Power supply unit |
| Plug-in power supply / adapter for countries - included with the delivery | EURO UK US CH |

| | |
|---|----------------------------------|
| Plug-in power supply / adapter for countries - optional | EURO UK US CH |
| Rechargeable battery optional | Rchrg. battery optional - intern |
| Rechargeable battery charging time | 8 h |
| Rechargeable battery operating time - backlight on | 24 h |
| Rechargeable battery operating time - backlight off | 48 h |

| Environmental conditions | |
|-------------------------------|--------|
| Humidity of environment [Max] | 80 % |
| Ambient temperature [Min] | -10 °C |
| Ambient temperature [Max] | 40 °C |

Packing & Shipping

| | |
|------------------------------|----------------|
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 520×390×150 mm |
| Net weight | 7,5 kg |
| Shipping method | Parcel service |
| Net weight approx. | 8 kg |
| Gross weight approx. | 10 kg |
| Shipping weight | 9,8 kg |

Services (optional)

| | |
|---|---------|
| Article number for DAkks calibration | 963-128 |
| Article number for certificate of conformity (verification) | 969-517 |

Pictograms

STANDARD



OPTION

