

KERN CIB 10K-3

Robust counting scale with large article memory, convenient operating philosophy and checkweighing display, counting resolution up to 30,000 points



Display digit height	18 mm
----------------------	-------

Construction

Dimension housing (W×D×H)	350×330×120 mm
Material housing	plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	315×215 mm
Display device cable length	5 m
Levelling feet adjustable	✓

Functions

Number of keys for operation	34
PreTare function	✓
Tare function	manual (multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Recipe/summing level	Sum A
IP protection - load cell	IP65

Counting

Smallest piece weight when piece counting - laboratory conditions	500 mg
Smallest piece weight when piece counting - normal conditions	5 g
Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)
Counting resolution (laboratory conditions)	30.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V AC 50/60 Hz 0.4 A max
Input voltage device / power [Max]	12 V, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Accu & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery charging time	14 h

Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	CIB

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	15 kg
Readability [d]	0,001 kg
Resolution	15.000
Linearity	± 0,002 kg
Reproducibility	0,001 kg
Tare range	15 kg
Default unit	kg
Units	kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (M1)
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,003 kg
Maximum creep (15 minutes)	4 g
Maximum creep (30 minutes)	8 g

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display backlight	blue, yellow, green, red

KERN CIB 10K-3



Robust counting scale with large article memory, convenient operating philosophy and checkweighing display, counting resolution up to 30,000 points

Rechargeable battery operating time - backlight on	90 h
Rechargeable battery operating time - backlight off	160 h
Battery / accumulator type	Pb
Battery connection	Plug-in terminals

Environmental conditions

Humidity of environment [Min]	15 %
Humidity of environment [Max]	85 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	385×400×150 mm
Net weight	3,99 kg
Shipping method	Parcel service
Net weight approx.	4,0 kg
Gross weight approx.	6 kg
Shipping weight	5,184 kg

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

