

KERN DS 10K0.1S

Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications



Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display screen size	89×30 mm
Display backlight	✓
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction

Dimension display device (W×D×H)	225×115×60 mm
Dimension housing (W×D×H)	225×115×60 mm
Dimensions weighing platform (W×D×H)	230×230×103 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material platform	metal, lacquered
Dimensions weighing surface (W×D)	228×228 mm
Display device cable length	2,5 m
Transport safety lock - bolt torque	0,1 Nm
Levelling feet adjustable	✓
Wall mount	✓
Stand height	450 mm

Functions

Number of keys for operation	5
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min 2 min 1 min 30 min 60 min 30 sec
PreTare function	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual

Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	DS

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	10 kg
Readability [d]	0,0001 kg
Resolution	100.000
Linearity	± 0,0003 kg
Reproducibility	0,0001 kg
Default unit	kg

Units	kg
	g
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
	lb
	oz ffa

Adjustment options	Adjusting with external weight
Recommended adjusting weight	10 kg (F1)
Possible calibration points	2 kg; 5 kg; 10 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,0005 kg

KERN DS 10K0.1S



Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications

Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Rez A (Net total)
Underfloor weighing	None
Interfaces	RS-232 (optional) Ethernet (optional) Bluetooth BLE (v4.0) (optional) USB-Device (optional) KUP WiFi (optional)

Counting	
Smallest piece weight when piece counting - laboratory conditions	100 mg
Smallest piece weight when piece counting - normal conditions	1 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	100.000

Power Supply	
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h

Environmental conditions	
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C

Ambient temperature [Max]	40 °C
---------------------------	-------

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	370×370×220 mm
Net weight	4,1 kg
Shipping method	Parcel service
Net weight approx.	4,2 kg
Gross weight approx.	5,0 kg
Shipping weight	6 kg

Services (optional)	
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

