

IoT-Line Precision Platform Scale KERN DS



Precision industrial scale with laboratory accuracy, ideal for the diverse possibilities of Industry 4.0 applications

Features

- High-capacity precision balance, ideal for high volume or heavy samples to be weighed with a high degree of accuracy
- Numerical subtraction of tare weight for known container weight. Useful for checking fill-levels
- Precise counting: The automatic reference weight optimisation of reference weight gradually improves the average piece weight value
- Freely programmable weighing unit, e.g. display direct in special units such as length of wire g/m, surface weight g/m², or else
- KERN Universal Port (KUP): permits the connection of an external KUP interface adapter, such as, for example, RS-232, USB, Bluetooth, WiFi or Ethernet, for the exchange of data and control commands, without any installation outlay

- KERN Communication Protocol (KCP): The KCP permits searching and remote control of the balance using external control devices or computers
- Protective working cover included with delivery

Technical data

- Large backlit LCD display, digit height 21 mm
- Weighing plate dimensions, stainless steel
 - A** W×D×H 230×230×103 mm
 - B** W×D×H 308×318×75 mm
 - C** W×D×H 500×400×125 mm, see larger picture
- Dimensions of display device W×D×H 225×115×60 mm
- Permissible ambient temperature -10 °C/40 °C

Accessories

- Internal rechargeable battery pack, operating time up to 24 h with backlight, charging time approx. 8 h, KERN YKR-01

- Protective working cover over the display device, scope of delivery: 5 items, KERN DE-A12S05
- **1** Column to screw on to the platform for models with weighing plate size **B**, **C**, height of stand approx. 480 mm, KERN DE-A10 for models with weighing plate size **A**, height of stand approx. 600 mm, KERN DS-A03
- Mount to fasten the display device to the platform, for models with weighing plate size **B**, **C**, **D**, **E**, KERN DE-A11N
- Wall mount for display device, KERN DS-A02
- **2** Set for underfloor weighing, consists of platform, bow, hook, only for models with weighing plate **B**, KERN DS-A01
- External data interface RS-232, interface cable included, KERN KUP-01
- External data interface USB, interface cable included, KERN KUP-03
- External data interface Ethernet, KERN KUP-04
- External data interface WiFi, interface cable included, KERN KUP-05
- Bluetooth interface adapter, KERN KUP-06
- Extension box for connecting up to three interfaces in parallel, KERN KUP-13
- Further details, plenty of further accessories and suitable printers see *Accessories*

STANDARD



OPTION



Model	Weighing capacity [Max] kg	Readability [d] g	Smallest part weight (Normal) g/piece	Resolution Points	Cable length approx. m	Net weight approx. kg	Weighing plate	Options	
								DAKKS	Calibr. Certificate KERN
DS 3K0.01S	3	0,01	0,1	300.000	2	4,2	A	963-127	
DS 5K0.05S	5	0,05	0,1	100.000	2	4,2	A	963-127	
DS 8K0.05	8	0,05	0,5	160.000	2	8	B	963-128	
DS 10K0.1S	10	0,1	1	100.000	2	4,2	A	963-128	
DS 16K0.1	16	0,1	1	160.000	2	8	B	963-128	
DS 20K0.1	20	0,1	1	200.000	2	8	B	963-128	
DS 30K0.1	30	0,1	1	300.000	2	8	B	963-128	
DS 30K0.1L	30	0,1	1	300.000	0,6	19	C	963-128	
DS 36K0.2	36	0,2	1	180.000	0,6	10	B	963-128	
DS 36K0.2L	36	0,2	1	180.000	0,6	19	C	963-128	
DS 60K0.2	60	0,2	2	300.000	0,6	19	C	963-129	
DS 65K0.5	65	0,5	2	130.000	0,6	19	C	963-129	
DS 100K0.5	100	0,5	5	200.000	0,6	19	C	963-129	
DS 150K1	150	1	10	150.000	0,6	19	C	963-129	

<p>Internal adjusting Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)</p>	<p>Interface for second balance For direct connection of a second balance</p>	<p>Hold function (Animal weighing program) When the weighing conditions are unstable, a stable weight is calculated as an average value</p>	<p>Conformity Assessment The time required for conformity assessment is specified in the pictogram</p>
<p>Adjusting program CAL For quick setting up of the balance's accuracy. External adjusting weight required</p>	<p>Network interface For connecting the scale to an Ethernet network</p>	<p>Protection against dust and water splashes IPxx The type of protection is shown in the pictogram</p>	<p>DAkkS calibration possible (DKD) The time required for DAkkS calibration is shown in days in the pictogram</p>
<p>EasyTouch Suitable for the connection, data transmission and control through PC or tablet</p>	<p>KERN Communication Protocol (KCP) It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems</p>	<p>Suspended weighing Load support with hook on the underside of the balance</p>	<p>Factory calibration (ISO) The time required for Factory calibration is shown in days in the pictogram</p>
<p>Memory Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.</p>	<p>GLP/ISO log intern The balance displays weight, date and time, independent of a printer connection</p>	<p>Battery operation Ready for battery operation. The battery type is specified for each device</p>	<p>Package shipment The time required for internal shipping preparations is shown in days in the pictogram</p>
<p>Alibi memory Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.</p>	<p>GLP/ISO log Printer With weight, date and time. Only with KERN printers.</p>	<p>Rechargeable battery pack Rechargeable set</p>	<p>Pallet shipment The time required for internal shipping preparations is shown in days in the pictogram</p>
<p>KERN Universal Port (KUP) allows the connection of external KUP interface adapters, e.g. RS-232, RS-485, SB, Bluetooth, WIFI, Analogue, Ethernet etc. for the exchange of data and control commands, without installation effort</p>	<p>Piece counting Reference quantities selectable. Display can be switched from piece to weight</p>	<p>Universal plug-in power supply with universal input and optional input socket adapters for A) EU, CH, GB B) EU, CH, GB, US C) EU, CH, GB, US, AUS</p>	
<p>RS-232 Data interface To connect the balance to a printer, PC or network</p>	<p>Recipe level A The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out</p>	<p>Plug-in power supply 230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available</p>	
<p>RS-485 Data interface To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible</p>	<p>Recipe level B Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display</p>	<p>Integrated power supply unit Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request</p>	
<p>USB Data interface To connect the balance to a printer, PC or other peripherals</p>	<p>Totalising level A The weights of similar items can be added together and the total can be printed out</p>	<p>Weighing principle Strain gauges Electrical resistor on an elastic deforming body</p>	
<p>Bluetooth* Data interface To transfer data from the balance to a printer, PC or other peripherals</p>	<p>Percentage determination Determining the deviation in % from the target value (100 %)</p>	<p>Weighing principle Tuning fork A resonating body is electromagnetically excited, causing it to oscillate</p>	
<p>WIFI Data interface To transfer data from the balance to a printer, PC or other peripherals</p>	<p>Weighing units Can be switched to e.g. nonmetric units. See balance model. Please refer to KERN's website for more details</p>	<p>Weighing principle Electromagnetic force compensation Coil inside a permanent magnet. For the most accurate weighings</p>	
<p>Control outputs (optocoupler, digital I/O) To connect relays, signal lamps, valves, etc.</p>	<p>Weighing with tolerance range (Checkweighing) Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model</p>	<p>Weighing principle Single cell technology Advanced version of the force compensation principle with the highest level of precision</p>	
<p>Analogue interface to connect a suitable peripheral device for analogue processing of the measurements</p>			

* The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.