

KERN EFC 60K-3

Platform scale with integrated rechargeable battery pack, a bright LED display and a column for greatest ease of use



Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	EFC

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	60 kg
Readability [d]	0,005 kg
Resolution	12.000
Linearity	± 0,01 kg
Reproducibility	0,01 kg
Default unit	kg
Units	kg lb PCS
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (F2)
Possible calibration points	6 kg; 12 kg; 15 kg; 20 kg; 30 kg; 40 kg; 60 kg
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,015 kg
Maximum creep (15 minutes)	20 g
Maximum creep (30 minutes)	40 g
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	4-wire

Approval

CE mark	✓
---------	---

Display

Display type	LED segments
Display type	LED segments
Display screen size	165×64 mm
Display backlight	no
Display digit height - smallest digit	52 mm
Display digit height	52 mm
Languages of the user interface	Symbol language

Construction

Dimension display device (W×D×H)	252×162×57 mm
Dimensions weighing platform (W×D×H)	400×300×124 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material platform	steel, varnished
Dimensions weighing surface (W×D)	400×300 mm
Display device cable length	3 m
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Stand height	600 mm
Stand rotatable	✓
Stand inclinable	✓

Functions

Number of keys for operation	7
Tare function	manual (single & multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Recipe/summing level	Sum A
Sum memory function	✓
Interfaces	RS-232 standard
IP protection - display	no IP protection

KERN EFC 60K-3

KERN

Platform scale with integrated rechargeable battery pack, a bright LED display and a column for greatest ease of use

Counting

Smallest piece weight when piece counting - laboratory conditions	2,5 g
Smallest piece weight when piece counting - normal conditions	25 g
Counting reference weight can be entered	✓
Reference quantity	n (any number of pieces)
Counting resolution (laboratory conditions)	24.000

Power Supply

Input voltage power supply / power [Max]	100 - 240 V 50/60 Hz 0.5 A
Input voltage device / power [Max]	5 V, 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Accu & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO UK
Plug-in power supply / adapter for countries - optional	EURO UK
Rechargeable battery operating time - backlight on	30 h
Rechargeable battery operating time - backlight off	50 h
Battery / accumulator type	Li-Ion
Battery capacity	4.000 mAh
Battery voltage	3,7 V

Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	800×465×230 mm
Net weight	8 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	10 kg
Shipping weight	17,1 kg

Services (optional)

Article number for adjustment at the location of installation	961-249
---	---------

Article number for DAkkS calibration 963-129

Article number for certificate of conformity (verification) 969-517

Pictograms

STANDARD



OPTION

