


IoT-Line Bench Scale KERN FCB



NEW



Technical data

- Backlit LCD display, digit height 25 mm
- Dimensions weighing surface, stainless steel, WxD 252x225 mm
- Overall dimensions WxDxH 322x267x91 mm
- Net weight approx. 3,8 kg
- Permissible ambient temperature
- KERN FCB: 0 °C/40 °C
- KERN FCB-M: -10 °C/40 °C

Accessories

- Protective working cover, scope of delivery 5 items, KERN YBA-A14S05
- Internal rechargeable battery pack, operating time up to 48 h without backlight, charging time approx. 8 h, KERN YKR-01
- **1** Signal lamp for visual support of weighing with tolerance range. connection is only possible in combination with KUP-01 (RS-232 interface), KERN CFS-A03
- External data interface RS-232, interface cable included, KERN KUP-01
- External data interface USB, interface cable included, KERN KUP-03
- Ethernet interface adapter, KERN KUP-04
- WiFi interface adapter, KERN KUP-05
- Bluetooth interface adapter, KERN KUP-06
- **2** Extension box for connecting up to three interfaces in parallel, KERN KUP-13

The new FCB: Checkweighing and portioning scale with up to three interfaces, with optional verification

Features

- Standardised, convenient KERN concept of operation, consistency across products in terms of design, menu structure, button functions, interface connection and interface protocol
- Compact size, practical for small spaces
- Industry 4.0: Data and control commands can be exchanged through the KERN Universal Port (KUP) using one interface, which can be connected to the housing, or through three parallel interfaces using the KUP Extension box. The following interfaces are available as an option: RS-232, USB, Ethernet, WiFi, Bluetooth

- Data query and remote control of the balance using a computer or CRM/ERP systems using the KERN Communication Protocol
- High mobility: Thanks to battery operation/rechargeable battery operation (optional), compact, lightweight construction, it is suitable for the use in several locations (production, warehouse, dispatch department, etc.)
- Weighing with tolerance range (checkweighing): Input of two upper and two lower limit values through four arrow keys. An audible and visual signal assists with the portioning, dispensing or grading
- Summation of weight values
- Protective working cover included with delivery

STANDARD



OPTION



Model	Weighing capacity [Max]	Readability	Verification value	Minimal load	Smallest part weight (Normal)	Options	
						Verification	DAkkS Calibr. Certificate
KERN	kg	[d] g	[e] g	[Min] g	g/piece	KERN	DAkkS KERN
FCB 6K-5	6	0,05	-	-	0,5	-	963-128
FCB 8K0.1	8	0,1	-	-	1	-	963-128
FCB 12K-4	12	0,1	-	-	1	-	963-128
FCB 12K1	12	1	-	-	10	-	963-128
FCB 30K-4	30	0,2	-	-	2	-	963-128
FCB 30K1	30	1	-	-	10	-	963-128
Multi-division balance, with increasing or decreasing load, it switches automatically to the next largest or smallest weighing range [Max] and readout [d].							
FCB 6K-3DM	3 6	1 2	1 2	20	2	965-228	963-128
FCB 15K-3DM	6 15	2 5	2 5	40	5	965-228	963-128
FCB 30K-3DM	15 30	5 10	5 10	100	10	965-228	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.

NEW New model

CAL INT **Internal adjusting**
Quick setting up of the balance's accuracy with internal adjusting weight (motordriven)

CAL EXT **Adjusting program CAL**
For quick setting up of the balance's accuracy. External adjusting weight required

ET **EasyTouch**
Suitable for the connection, data transmission and control through PC or tablet

MEMORY **Memory**
Balance memory capacity, e.g. for article data, weighing data, tare weights, PLU etc.

ALIBI **Alibi memory**
Secure, electronic archiving of weighing results, complying with the 2014/31/EU standard.

KUP **KERN Universal Port (KUP)**
allows the connection of external KUP interface adapters, e.g. RS-232, RS-485, SB, Bluetooth, WIFI, Analogue, Ethernet etc. for the exchange of data and control commands, without installation effort

RS 232 **RS-232 Data interface**
To connect the balance to a printer, PC or network

RS 485 **RS-485 Data interface**
To connect the balance to a printer, PC or other peripherals. Suitable for data transfer over large distances. Network in bus topology is possible

USB **USB Data interface**
To connect the balance to a printer, PC or other peripherals

BT **Bluetooth* Data interface**
To transfer data from the balance to a printer, PC or other peripherals

WIFI **WIFI Data interface**
To transfer data from the balance to a printer, PC or other peripherals

SWITCH **Control outputs**
(optocoupler, digital I/O)
To connect relays, signal lamps, valves, etc.

D/A ANALOG **Analogue interface**
to connect a suitable peripheral device for analogue processing of the measurements

DUAL **Interface for second balance**
For direct connection of a second balance

LAN **Network interface**
For connecting the scale to an Ethernet network

KCP PROTOCOL **KERN Communication Protocol (KCP)**
It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems

GLP INTERN **GLP/ISO log intern**
The balance displays weight, date and time, independent of a printer connection

GLP PRINTER **GLP/ISO log Printer**
With weight, date and time. Only with KERN printers.

PCS **Piece counting**
Reference quantities selectable. Display can be switched from piece to weight

RECIPE **Recipe level A**
The weights of the recipe ingredients can be added together and the total weight of the recipe can be printed out

RECIPE **Recipe level B**
Internal memory for complete recipes with name and target value of the recipe ingredients. User guidance through display

SUM **Totalising level A**
The weights of similar items can be added together and the total can be printed out

PERCENT **Percentage determination**
Determining the deviation in % from the target value (100 %)

UNIT **Weighing units**
Can be switched to e.g. nonmetric units. See balance model. Please refer to KERN's website for more details

TOL **Weighing with tolerance range (Checkweighing)**
Upper and lower limiting can be programmed individually, e.g. for sorting and dosing. The process is supported by an audible or visual signal, see the relevant model

MOVE **Hold function**
(Animal weighing program)
When the weighing conditions are unstable, a stable weight is calculated as an average value

IP **Protection against dust and water splashes IPxx**
The type of protection is shown in the pictogram

UNDER **Suspended weighing**
Load support with hook on the underside of the balance

BATT **Battery operation**
Ready for battery operation. The battery type is specified for each device

ACCU **Rechargeable battery pack**
Rechargeable set

MULTI **Universal plug-in power supply**
with universal input and optional input socket adapters for
A) EU, CH, GB
B) EU, CH, GB, US
C) EU, CH, GB, US, AUS

230 V **Plug-in power supply**
230V/50Hz in standard version for EU, CH. On request GB, USA or AUS version available

230 V **Integrated power supply unit**
Integrated in balance. 230V/50Hz standard EU. More standards e.g. GB, USA or AUS on request

DMS **Weighing principle Strain gauges**
Electrical resistor on an elastic deforming body

T-FORK **Weighing principle Tuning fork**
A resonating body is electromagnetically excited, causing it to oscillate

FORCE **Weighing principle Electromagnetic force compensation**
Coil inside a permanent magnet. For the most accurate weighings

SC TECH **Weighing principle Single cell technology**
Advanced version of the force compensation principle with the highest level of precision

M +3 DAYS **Conformity Assessment**
The time required for conformity assessment is specified in the pictogram

DAkkS +3 DAYS **DAkkS calibration possible (DKD)**
The time required for DAkkS calibration is shown in days in the pictogram

ISO +4 DAYS **Factory calibration (ISO)**
The time required for Factory calibration is shown in days in the pictogram

1 DAY **Package shipment**
The time required for internal shipping preparations is shown in days in the pictogram

2 DAYS **Pallet shipment**
The time required for internal shipping preparations is shown in days in the pictogram

*The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.