

KERN FKB 6K0.02



High resolution bench scale with large weighing range and robust stainless steel weighing plate



Category

Brand	KERN
Product category	Industrial scale
Product group	Bench scale
Product family	FKB

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	6 kg
Readability [d]	0,00002 kg
Resolution	300.000
Linearity	± 0,0001 kg
Reproducibility	0,00004 kg
Default unit	kg

Units	kg
	g
	gn
	dwt
	ozt
	lb
	oz
	ffa

Adjustment options	Adjusting with external weight
Recommended adjusting weight	5 kg (F1); 1 kg (F1)
Possible calibration points	2 kg; 4 kg; 6 kg
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,0001 kg
Maximum creep (15 minutes)	200 mg
Maximum creep (30 minutes)	400 mg

Zulassung

CE mark	✓
---------	---

Display

Display type	LCD
Display screen size	120×38 mm
Display backlight	✓
Display digit height	25 mm
Languages of the user interface	English Symbol language

Construction

Dimension housing (W×D×H)	350×390×120 mm
Dimensions weighing platform (W×D×H)	340×240×21 mm
Material display housing	Plastics
Material housing	ABS plastic
Material weighing plate	stainless steel
Dimensions weighing surface (W×D)	340×240 mm
Levelling feet adjustable	✓
Level indicator	✓

Functions

Number of keys for operation	6
Auto-off interval(s) in mains power mode	off
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
	30 sec
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓

Tolerance weighing - type of signal	acoustically visual
-------------------------------------	------------------------

Function for averaging under unstable weighing conditions	✓
Conversion function	✓
Recipe/summing level	Sum A

Underfloor weighing	Hook (included in delivery)
---------------------	-----------------------------

Interfaces	RS-232 (optional)
	Ethernet (optional)
	Bluetooth BLE (v4.0) (optional)

KERN FKB 6K0.02



High resolution bench scale with large weighing range and robust stainless steel weighing plate

	USB-Device (optional) KUP WiFi (optional)
IP protection - display	no IP protection

Counting

Smallest piece weight when piece counting - laboratory conditions	20 mg
Smallest piece weight when piece counting - normal conditions	200 mg
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	300.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Rechargeable battery optional	Rchrg. battery optional - intern
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Battery	4×1.5 V AA
Battery / accumulator type	Li-Ion
Battery connection	Battery insert
Battery operating time	20 h

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	470×470×190 mm
Net weight	6,5 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	8 kg
Shipping weight	8,4 kg

Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

