

# KERN HFD 3T-3IP

Robust, high-resolution crane scale, with protection type IP67



## Category

Brand	KERN
Product category	Industrial scale
Product group	Crane scale
Product family	HFD

## Measuring System

Construction type of the scale	Multi-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	600 kg; 1500 kg; 3000 kg
Readability [d]	0,2 kg; 0,5 kg; 1 kg
Resolution	3.000, 3.000, 3.000
Linearity	± 0,4 kg; 1 kg; 2 kg
Reproducibility	0,2 kg; 0,5 kg; 1 kg
Tare range	2999 kg
Default unit	kg
Units	kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	3000 kg (M1)
Possible calibration points	3000 kg
Stabilization time	2 s
Warm-up time	10 min; 10 min; 10 min
Eccentric/Off-centre loading is not possible	✓
Maximum creep (15 minutes)	4 kg
Maximum creep (30 minutes)	8 kg
Loadcell type	HS-16 5T
Load cell connection	4-wire
Tolerance (% of [Max])	0,2%
Internal measuring frequency	10 Hz

## Approval

CE mark	✓
---------	---

## Display

Display type	LCD
Display screen size	115 x40 mm
Display backlight	LED white
Display digit height	30 mm
Languages of the user interface	Symbol language

## Construction

Dimension display device (W×D×H)	194×160×129 mm
Dimensions housing - width (A)	194 mm
Dimensions housing - depth (B)	129 mm
Dimensions housing - height/length (C)	160 mm
Dimensions - total height/total length (D)	457 mm
Dimensions hook/bottom - hole diameter (G)	58 mm
Dimensions - inner length (E)	413 mm
Dimensions loop/top - hole diameter (F)	58 mm
Dimensions completely mounted (W×D×H)	457×194×145 mm
Material housing	cast aluminium
Material load hook	unalloyed forged steel
Material suspension	unalloyed forged steel
Material load cell(s)	high-alloy steel
Load cells - number	1

## Functions

Number of keys for operation	5
Auto-off interval(s) in mains power mode	selectable
	3 min
Auto-off interval(s) in battery mode/rechargeable battery mode	off
	5 min
	15 min
Wireless operation	✓
Capacity - Display	✓
Tare function	manual (single & multi)
Standby function	✓
Range of radio module	20 m
Recipe/summing level	Sum A
Sum memory function	✓
IP protection - complete device	IP67

# KERN HFD 3T-3IP



Robust, high-resolution crane scale, with protection type IP67

## Power Supply

Input voltage power supply / power [Max]	110 V - 240 V AC
Input voltage device / power [Max]	12 V, 2500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Accu & Power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO UK CH
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	30 h
Rechargeable battery operating time - backlight off	70 h
Battery	1×12 V, Type 23 A
Battery / accumulator type	Li-Ion
Battery connection	Plug-in terminals
Battery capacity	5.200 mAh

## Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	715×275×265 mm
Net weight	10 kg
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	12 kg
Shipping weight	12 kg

## Services (optional)

Article number for adjustment at the location of installation	961-252
Article number for DAkkS calibration	963-132H
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION

