

KERN IFB 60K-3

High-resolution industrial scale in heavy version



Approval

CE mark ✓

Display

Display type LCD
 Display backlight ✓
 Display digit height 52 mm
 Languages of the user interface Symbol language

Construction

Dimension display device (W×D×H) 250×160×58 mm
 Dimensions weighing platform (W×D×H) 400×300×117 mm
 Dimensions completely mounted (W×D×H) 400×300×120 mm
 Material display housing Plastics
 Material housing plastic
 Material weighing plate stainless steel
 Material platform steel, powder-coated
 Dimensions weighing surface (W×D) 400×300 mm
 Display device cable length 3 m
 Allowed cable length display device [Max] 20 m
 Material load cell(s) aluminium
 Load cells - number 1
 Levelling feet adjustable ✓
 Wall mount ✓
 Stand height 600 mm
 Stand inclinable ✓

Functions

Number of keys for operation 7
 Auto-off interval(s) in mains power mode off, 5 min, 15 min
 Auto-off interval(s) in battery mode/rechargeable battery mode off, 5 min, 15 min
 Tare function manual (single & multi)
 Counting function ✓
 Tolerance weighing ✓
 Tolerance weighing - type of signal acoustically, visual
 Function for averaging under unstable weighing conditions ✓
 Recipe/summing level Sum A
 Sum memory function ✓

Category

Brand KERN
 Product category Industrial scale
 Product group Platform scale
 Product family IFB

Measuring System

Construction type of the scale Single-range balance
 Weighing system Strain gauge
 Weighing capacity [Max] 60 kg
 Readability [d] 0,002 kg
 Resolution 30.000
 Linearity ± 0,008 kg
 Reproducibility 0,002 kg
 Default unit kg
 Units kg, g, lb, Hj, tj, lb:oz
 Adjustment options Adjusting with external weight
 Recommended adjusting weight 60 kg (F2)
 Stabilization time 2 s
 Warm-up time 120 min
 Eccentric loading at 1/3 [Max] 0,01 kg
 Maximum creep (15 minutes) 8 g
 Maximum creep (30 minutes) 16 g
 Loadcell type aluminium IP65 silicone-coated
 Load cell connection 4-wire

KERN IFB 60K-3



High-resolution industrial scale in heavy version

Interfaces	RS-232 standard Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - load cell	IP65
IP protection - platform	no IP protection

Counting

Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	60.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	35 h
Battery	no battery
Battery / accumulator type	Pb

Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	470×794×229 mm
Net weight	6,33 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	9 kg
Shipping weight	17,1 kg

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

