

KERN IFB 60K-3L

High-resolution industrial scale in heavy version



Category

Brand	KERN
Product category	Industrial scale
Product group	Platform scale
Product family	IFB

Measuring System

Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	60 kg
Readability [d]	0,002 kg
Resolution	30.000
Linearity	± 0,008 kg
Reproducibility	0,002 kg
Default unit	kg

Units	kg
	g
	lb
	Hj, tj
	lb:oz

Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (F2)
Stabilization time	2 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,01 kg
Maximum creep (15 minutes)	8 g
Maximum creep (30 minutes)	16 g
Loadcell type	aluminium IP65 silicone-coated
Load cell connection	6-wire

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display backlight	✓
Display digit height	52 mm
Languages of the user interface	Symbol language

Construction

Dimension display device (W×D×H)	250×160×58 mm
Dimensions weighing platform (W×D×H)	500×400×127 mm
Dimensions completely mounted (W×D×H)	500×400×130 mm
Material display housing	Plastics
Material housing	plastic
Material weighing plate	stainless steel
Material platform	steel, powder-coated
Dimensions weighing surface (W×D)	500×400 mm
Display device cable length	3 m
Allowed cable length display device [Max]	3 m
Material load cell(s)	aluminium
Load cells - number	1
Levelling feet adjustable	✓
Wall mount	✓
Stand height	600 mm
Stand inclinable	✓

Functions

Number of keys for operation	7
Auto-off interval(s) in mains power mode	off 5 min 15 min
Auto-off interval(s) in battery mode/rechargeable battery mode	off 5 min 15 min
Tare function	manual (single & multi)
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Sum memory function	✓

KERN IFB 60K-3L



High-resolution industrial scale in heavy version

Interfaces	RS-232 standard Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - load cell	IP65
IP protection - platform	no IP protection

Counting

Smallest piece weight when piece counting - laboratory conditions	2 g
Smallest piece weight when piece counting - normal conditions	20 g
Reference quantity	10, 20, 50, 100, 200
Counting resolution (laboratory conditions)	30.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	12 V, 500 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Rechargeable battery optional	Rchrg. battery optional
Rechargeable battery charging time	12 h
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	35 h
Battery	no battery
Battery / accumulator type	Pb

Environmental conditions

Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C

Packing & Shipping


Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	555×930×215 mm
Net weight	11 kg
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	16 kg
Shipping weight	22,2 kg

Services (optional)

Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

