

KERN TN 30-0.01EE

KERN

Hand-held measuring device for ultrasonic material thickness testing in Echo-Echo principle



Category

Brand	Sauter
Product category	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge Echo-Echo Method
Product family	TN-EE

Measuring System

Units	mm inch
Tolerance (% of [Max])	0,5%
Readability material thickness [d] (mm)	0,01 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Material thickness pulse-echo [Min] (mm)	0,65 mm
Material thickness pulse-echo [Max] (mm)	600 mm
Material thickness echo-echo [Min] (mm)	3 mm
Material thickness echo-echo [Max] (mm)	30 mm
Measuring head diameter	10 mm
Measuring head measuring frequency	5 MHz
Internal data memory: Number of value groups	20
Internal data memory: Number of individual values	100

Approval

CE mark	✓
---------	---

Display

Display type	LCD
Display digit height	14 mm

Construction

Dimension (W×D×H)	150×74×32 mm
Dimension housing (W×D×H)	150×74×32 mm
Dimensions completely mounted (W×D×H)	150×74×32 mm
Material housing	plastic
Cable length	0,9 m

Functions

Memory function	✓
Interfaces	USB-Device

Power Supply

Supplied power supply	Battery
Battery	2×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery capacity	3.000 mAh
Battery voltage	1,5 V
Battery operating time	100 h

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	320×248×85 mm
Net weight	0,245 kg
Shipping method	Parcel service
Net weight approx.	0,25 kg
Gross weight approx.	1,4 kg
Shipping weight	1,33 kg

Services (optional)

Article number for factory calibration	961-113
--	---------


KERN TN 30-0.01EE



Hand-held measuring device for ultrasonic material thickness testing in Echo-Echo principle

Pictograms

STANDARD



OPTION

