

# KERN TN 300-0.01US

**KERN**

Portable measuring device for ultrasonic material thickness testing



Display digit height 14 mm

## Construction

Dimension (W×D×H)	150×74×32 mm
Dimension housing (W×D×H)	150×74×32 mm
Dimensions completely mounted (W×D×H)	150×74×32 mm
Material housing	plastic
Cable length	0,9 m

## Functions

Interfaces USB-Device

## Power Supply

Supplied power supply	Battery
Battery	2×1.5 V AA
Battery / accumulator type	Alkali(-Manganese)
Battery capacity	3.000 mAh
Battery voltage	1,5 V
Battery operating time	100 h

## Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	315×245×90 mm
Net weight	0,272 kg
Shipping method	Parcel service
Net weight approx.	0,30 kg
Gross weight approx.	1,4 kg
Shipping weight	1,4 kg

## Services (optional)

Article number for factory calibration	961-113
--	---------

## Category

Brand	Sauter
Product category	Material thickness measuring device
Product group	Ultrasonic Material thickness gauge pulse-echo method
Product family	TN-US

## Measuring System

Units	mm inch
Tolerance (% of [Max])	0,5%
Readability material thickness [d] (mm)	0,01 mm
Speed of sound [Min] (m/s)	1000 m/s
Speed of sound [Max] (m/s)	9999 m/s
Material thickness pulse-echo [Min] (mm)	3 mm
Material thickness pulse-echo [Max] (mm)	300 mm
Measuring head diameter	14 mm
Measuring head measuring frequency	2,5 MHz
Internal data memory: Number of value groups	20
Internal data memory: Number of individual values	100

## Approval

CE mark ✓

## Display

Display type LCD

# KERN TN 300-0.01US


Portable measuring device for ultrasonic material thickness testing



## Pictograms

### STANDARD

---



### OPTION

---

