

Polarimeter KERN OAB-L



The ideal helper for getting started with the analysis of your optically active solutions in the laboratory

Features

- The models of the serie KERN OAB-L are manual polarimeters which are characterised by its ergonomic design and easy handling
- The powerful 589 nm sodium vapour lamp is the optimum light source to produce a linear, polarised beam of light
- The 1° scale division including Nonius (0.05°) enables precise definition of the angle of rotation of the substance to be observed
- To hold liquid samples, two glass cuvettes (100 mm/200 mm) are included with the delivery
- Included with delivery:
Sodium vapour lamp, 100 mm glass cuvette, 200 mm glass cuvette, replacement lenses and sealing rings for cuvettes

Technical data

- Light source: Sodium vapour lamp (589 nm)
- Stabilisation time: 10 mins after switching on
- Total dimensions W×D×H
430×140×310 mm
- Net weight approx. 3,5 kg

STANDARD



Polarimeter KERN OAB-L

Scope of application: Laboratory/Education

The reliable polarimeters in the OAB-L range have been designed for simple laboratory applications as well as practical training. You can evaluate liquid, optically-active samples with chiral characteristics with this device. Typical applications are determining kinetics in cane sugar inversion, determining mutarotation of glucose and investigation of starch hydrolysis. The optical rotation is measured in degrees.

The main scope of applications is:

- Pharmacy
- Sugar industry: for example cane sugar
- Beverage industry
- Food industry
- Chemical industry
- Laboratories
- Training



Cuvette in measuring chamber

Model	Scales	Measuring range	Division	Vernier	Wave length
KERN					
OAB 10LN*	Optical rotation	± 180°	1°	0,05°	589 nm

■ *ONLY WHILE STOCKS LAST

Accessory parts: OAB

Model	Description
KERN	
OAB-A2501	Glass cuvette, Length: 100 mm (Spare part)
OAB-A2502	Glass cuvette, Length: 200 mm (Spare part)
OAB-A2581*	Sodium vapour lamp, Wave length: 589 mm (Spare part)

*For model OAB 10LN only



Cuvette 10 and 20 cm

360° rotatable microscope head	Fluorescence illumination for compound microscopes With 100 W mercury lamp and filter	Integrated scale In the eyepiece	Battery operation Ready for battery operation. The battery type is specified for each device.
Monocular Microscope For the inspection with one eye	Fluorescence illumination for compound microscopes With 3 W LED illumination and filter	SD card For data storage	Battery operation rechargeable Prepared for a rechargeable battery operation
Binocular Microscope For the inspection with both eyes	Phase contrast unit For a higher contrast	USB 2.0 interface For data transmission	Plug-in power supply 230V/50Hz in standard version for EU. On request GB, AUS or USA version.
Trinocular Microscope For the inspection with both eyes and the additional option for the connection of a camera	Darkfield condenser/unit For a higher contrast due to indirect illumination	USB 3.0 interface For data transmission	Integrated power supply unit Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.
Abbe Condenser With high numerical aperture for the concentration and the focusing of light	Polarising unit To polarise the light	WIFI data interface: For transmitting of the picture to a mobile display device	Package shipment The time required to manufacture the product internally is shown in days in the pictogram.
Halogen illumination For pictures bright and rich in contrast	Infinity system Infinity corrected optical system	HDMI digital camera For direct transmitting of the picture to a display device	Pallet shipment The time required to manufacture the product internally is shown in days in the pictogram.
LED illumination Cold, energy-saving and especially long-life illumination	Zoom magnification For stereomicroscopes	PC software To transfer the measurements from the device to a PC.	
Incident illumination For non-transparent objects	Auto-focus For automatic control of the focus level	Automatic temperature compensation For measurements between 10 °C and 30 °C	
Transmitting illumination For transparent objects	Parallel optical system For stereomicroscopes, enables fatigue-proof working	Protection against dust and water splashes IPxx: The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013	
Fluorescence illumination For stereomicroscopes			

Abbreviations

C-Mount	Adapter for the connection of a camera to a trinocular microscope	SLR camera	Single-Lens Reflex camera
FPS	Frames per second	SWF	Super Wide Field (Field number at least \varnothing 23 mm for 10 \times eyepiece)
H(S)WF	High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)	W.D.	Working Distance
LWD	Long Working Distance	WF	Wide Field (Field number up to \varnothing 22 mm for 10 \times eyepiece)
N.A.	Numerical Aperture		