Video Microscope KERN OIV-6





Side view with screen connected (not included with delivery)



The professional video microscope with auto-focus

Features

- The Kern OIV-6 is a video microscope which has been constructed to optimise digital stereo microscopy. Our well-conceived, comprehensive solution with axial optical unit enables immediate, simple display of your samples on the screen
- The LED incident illumination unit (ring) included as standard guarantees the very best illumination of your sample
- · Combined with the large working surface, recording objects on the screen is ideally suited for monitoring, analysis and documentation suitable in the industrial sector
- The excellent optical unit enables continuous sharp image tracking across the entire zoom range from 0,7×-4,5×
- Through the integrated auto-focus, the focus level can also be optimised within a defined image section

- The powerful 2.0 megapixel camera of the microscope without eyepieces offers, thanks to the HDMI output, smooth live monitoring of your samples using an external monitor (not included with delivery). In addition, the software which is easy to use, the USB stick as well as the USB mouse which are integral components of the delivery, mean you can process and store your results digitally
- The OIV 656 guarantees software-controlled taking of images and videos with additional, documentation functions
- Multi-lingual user instructions are included in the scope of the delivery

Technical data

- · Optical system: Axial
- · Brightness adjustable
- Magnification ratio: 6,5:1
- · Stand: arm curved
- Illumination: 3 W LED ring (incident)
- Data storage: External using USB (Max 128 GB)
- · Working distance: 91 mm
- Maximum sample height: 85 mm
- Overall dimensions W×D×H 372×285×482 mm
- Net weight approx. 7 kg

Accessories

- Auxiliary objective 0,5×, KERN OZB-A6101
- Auxiliary objective 2,0×, KERN OZB-A6102



















Model	Standard configuration					
	Resolution	Interface	Sensor	Field of view	Objective	Software functions
KERN	camera			mm	Zoom	
OIV 656	2 MP	HDMI (30 FPS)	CMOS 1/2,8"	Ø 12,64-2,65	0,7×-4,5×	Images and videos, documentation

MICROSCOPES & REFRACTOMETERS 2024

KERN Pictograms





360° rotatable microscope head



Monocular MicroscopeFor the inspection with one eye



Binocular MicroscopeFor the inspection with both eyes



Trinocular MicroscopeFor the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination For pictures bright and rich in contrast



LED illumination

Cold, energy-saving and especially long-life illumination



Incident illuminationFor non-transparent objects



Transmitting illuminationFor transparent objects



Fluorescence illumination For stereomicroscopes



Fluorescence illumination for compound microscopes

With 100 W mercury lamp and filter



Fluorescence illumination for compound microscopes

With 3 W LED illumination and filter



Phase contrast unit

For a higher contrast



Darkfield condenser/ unit

For a higher contrast due to indirect illumination



Polarising unit
To polarise the light



Infinity system Infinity corrected optical system



Zoom magnification For stereomicroscopes



·



Auto-focus

For automatic control of the focus level



Parallel optical system For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD cardFor data storage



USB 2.0 interfaceFor data transmission



USB 3.0 interface For data transmission



WIFI data interface:

For transmitting of the picture to a mobile display device



HDMI digital camera

For direct transmitting of the picture to a display device



PC software

To transfer the measurementsfrom the device to a PC.



Automatic temperature compesation

For measurements between 10 °C and 30 °C



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999 +A2:2013



Battery operation

Ready for battery operation. The battery type is specified for each device.



Battery operation rechargeable

Prepared for a rechargeable battery operation



Plug-in power supply

230V/50Hz in standard version for EU.
On request GB, AUS or USA version.



Integrated power supply unit

Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.



Pallet shipment

The time required to manufacture the product internally is shown in days in the pictogram.

Abbreviations

C-Mount Adapter for the connection of a

camera to a trinocular microscope

FPS Frames per second

H(S)WF High (Super) Wide Field (Eyepiece with high eye

point for wearers of glasses)

LWD Long Working Distance

N.A. Numerical Aperture

SLR camera Single-Lens Reflex camera

SWF Super Wide Field (Field number at least Ø 23 mm

for 10× eyepiece)

W.D. Working Distance

WF Wide Field (Field number up to Ø 22 mm

for 10× eyepiece)