

Stereomicroscope KERN OSE-42



Side view

Educational Line

Stereo microscope with robust, ergonomic design, ideal for workshops, schools and training

Features

- With its integrated handle as well as its stable arm curved stand, the KERN OSE OSE-42 has been specially developed for schools and workshops
- The incident and transmitted illumination unit included as standard can be optionally enabled for the very best illumination of your sample. Mobile use is also no problem due to the integrated battery compartment
- Despite its low price it has very good optical characteristics, which enable you to have sharp images over a large field of view
- An turnable objective with predefined magnifications is available to make your working procedures quicker and more efficient

- The eyepieces are fixed in the eyepiece tube, to stop them getting damaged or lost
- A special feature of this adaptable and yet robust microscope series is the stable mechanism of the microscope stand which can be adjusted precisely. It will also impress you with its functionality and ergonomic design
- A large selection of eyepieces as well as various additional external illumination units are available as accessories

Scope of application

- Training, in vitro fertilisation, detection of parasites, zoology and botany, tissue preparation, section, quality control

Applications/Samples

- Samples with focus on three-dimensional impression (depth, thickness), e.g. insects, seeds, circuit boards, components

Technical data

- Optical system: Greenough optics
- Brightness adjustable
- Tube 45° inclined
- Interpupillary distance 55 – 75 mm
- Diopter adjustment: Both-sided
- Overall dimensions W×D×H 200×180×300 mm
- Net weight approx. 2 kg

STANDARD



Model

Model	Standard configuration					
	Tube	Eyepiece	Field of view mm	Objective	Stand	Illumination
KERN						
OSE 42 1	Binocular	WF 10×/ø 20 mm	ø 20	2×/4×	Arm curved	1 W LED (incident); 1 W LED (transmitted)

Stereomicroscope KERN OSE-42

Eyepiece

Specifications - Objectives

	Magnification	2×	4×
WF 5×	Total magnification	10×	20×
	Field of view mm	∅ 10	∅ 5
WF 10×	Total magnification	20×	40×
	Field of view mm	∅ 10	∅ 5
WF 15×	Total magnification	30×	60×
	Field of view mm	∅ 7,5	∅ 3,7
WF 20×	Total magnification	40×	80×
	Field of view mm	∅ 6,5	∅ 3,2
Working distance		57 mm	57 mm

Model outfit

Model KERN

Order number

		OSE 421	
Eyepieces (30,5 mm)	WF 5×/∅ 16,2 mm	○ ○	OZB-A4101
	WF 10×/∅ 20 mm	✓ ✓	OZB-A4102
	WF 15×/∅ 15 mm	○ ○	OZB-A4103
	WF 20×/∅ 10 mm	○ ○	OZB-A4104
	WF 10×/∅ 20 mm (reticule 0,1 mm)	○	OZB-A4151
Stand	Arm curved, with 1 W LED illumination (transmitted + incident)	✓	
Stage plate	Frosted glass/∅ 59,5 mm	✓	OZB-A4815
	Black-white/∅ 59,5 mm	✓	OZB-A4816
External illumination	Please find the information about external illumination units in the catalogue on page 87 and on the internet		

✓ = Included with delivery

○ = Option

360° rotatable microscope head	Fluorescence illumination for compound microscopes With 100 W mercury lamp and filter	Integrated scale In the eyepiece	Battery operation Ready for battery operation. The battery type is specified for each device.
Monocular Microscope For the inspection with one eye	Fluorescence illumination for compound microscopes With 3 W LED illumination and filter	SD card For data storage	Battery operation rechargeable Prepared for a rechargeable battery operation
Binocular Microscope For the inspection with both eyes	Phase contrast unit For a higher contrast	USB 2.0 interface For data transmission	Plug-in power supply 230V/50Hz in standard version for EU. On request GB, AUS or USA version.
Trinocular Microscope For the inspection with both eyes and the additional option for the connection of a camera	Darkfield condenser/unit For a higher contrast due to indirect illumination	USB 3.0 interface For data transmission	Integrated power supply unit Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.
Abbe Condenser With high numerical aperture for the concentration and the focusing of light	Polarising unit To polarise the light	WIFI data interface: For transmitting of the picture to a mobile display device	Package shipment The time required to manufacture the product internally is shown in days in the pictogram.
Halogen illumination For pictures bright and rich in contrast	Infinity system Infinity corrected optical system	HDMI digital camera For direct transmitting of the picture to a display device	Pallet shipment The time required to manufacture the product internally is shown in days in the pictogram.
LED illumination Cold, energy-saving and especially long-life illumination	Zoom magnification For stereomicroscopes	PC software To transfer the measurements from the device to a PC.	
Incident illumination For non-transparent objects	Auto-focus For automatic control of the focus level	Automatic temperature compensation For measurements between 10 °C and 30 °C	
Transmitting illumination For transparent objects	Parallel optical system For stereomicroscopes, enables fatigue-proof working	Protection against dust and water splashes IPxx: The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013	
Fluorescence illumination For stereomicroscopes			

Abbreviations

C-Mount	Adapter for the connection of a camera to a trinocular microscope	SLR camera	Single-Lens Reflex camera
FPS	Frames per second	SWF	Super Wide Field (Field number at least \varnothing 23 mm for 10 \times eyepiece)
H(S)WF	High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)	W.D.	Working Distance
LWD	Long Working Distance	WF	Wide Field (Field number up to \varnothing 22 mm for 10 \times eyepiece)
N.A.	Numerical Aperture		