

KERN PLJ 420-3F

Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples



Automatic adjustment - Standard temperature deviation	1,2 °C
---	--------

Stabilization time	3 s
--------------------	-----

Warm-up time	4 h
--------------	-----

Eccentric loading at 1/3 [Max]	0,004 g
--------------------------------	---------

Maximum creep (15 minutes)	10 mg
----------------------------	-------

Maximum creep (30 minutes)	20 mg
----------------------------	-------

Approval

CE mark	✓
---------	---

Display

Display type	LCD graphic
--------------	-------------

Display screen size	132×38 mm
---------------------	-----------

Display backlight	✓
-------------------	---

Display digit height - smallest digit	4 mm
---------------------------------------	------

Display digit height	15 mm
----------------------	-------

Languages of the user interface	English
---------------------------------	---------

Construction

Dimension housing (W×D×H)	210×340×120 mm
---------------------------	----------------

Dimensions ring-shaped draught shield - inner (Ø×H)	150×60 mm
---	-----------

Dimensions ring-shaped draught shield - outer (Ø×H)	160×70 mm
---	-----------

Dimensions completely mounted (W×D×H)	210×340×160 mm
---------------------------------------	----------------

Material housing	plastic
------------------	---------

Material weighing plate	stainless steel
-------------------------	-----------------

Material platform	Stainless steel
-------------------	-----------------

Material draught shield	glass
-------------------------	-------

Dimensions weighing surface (Ø)	110 mm
---------------------------------	--------

Transport safety lock - bolt torque	0,1 Nm
-------------------------------------	--------

Levelling feet adjustable	✓
---------------------------	---

Functions

Number of keys for operation	6
------------------------------	---

Auto-off interval(s) in mains power mode	off
--	-----

Auto-off interval(s) in mains power mode	5 min
--	-------

Auto-off interval(s) in mains power mode	2 min
--	-------

Auto-off interval(s) in mains power mode	15 min
--	--------

Capacity - Display	✓
--------------------	---

Time display	✓
--------------	---

PreTare function	✓
------------------	---

Tare function	manual (multi)
---------------	----------------

Density determination	✓
-----------------------	---

Percentage determination	✓
--------------------------	---

Counting function	✓
-------------------	---

Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PLJ

Measuring System

Construction type of the scale	Single-range balance
--------------------------------	----------------------

Weighing system	Strain gauge
-----------------	--------------

Weighing capacity [Max]	420 g
-------------------------	-------

Weighing capacity [Max] (ct)	2100 ct
------------------------------	---------

Readability [d]	0,001 g
-----------------	---------

Resolution	420.000
------------	---------

Linearity	± 0,003 g
-----------	-----------

Reproducibility	0,001 g
-----------------	---------

Tare range	420 g
------------	-------

Default unit	g
--------------	---

Units	g
	mg
	gn
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
lb	
oz	

USP Minimum weight of sample (k = 2, U = 0.1%)	2 g
--	-----

Adjustment options	Internal calibration (automatic)
--------------------	----------------------------------

KERN PLJ 420-3F



Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples

Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Recipe/summing level	Rez B (Net-total, memory with plain text designations + setpoint, also for printout)
Recipe weighing - number of database entries	99
Recipe weighing - number of ingredients per database entry	20
Underfloor weighing	None
Interfaces	RS-232 standard

Counting

Smallest piece weight when piece counting - laboratory conditions	5 mg
Smallest piece weight when piece counting - normal conditions	50 mg
Counting reference weight can be entered	✓
Reference quantity	10, 25, 50, 100, n (any number of pieces)
Counting resolution (laboratory conditions)	84.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH

Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	500×360×420 mm
Net weight	4,9 kg
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	8 kg
Shipping weight	15,1 kg

Services (optional)

Article number for DAkkS calibration	963-127
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

