

KERN PLJ 6200-2AM

Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples



USP Minimum weight of sample (k = 2, U = 0.1%)	20 g
Minimum weight [Min] (ct)	5 ct
Adjustment options	Internal calibration (automatic)
Automatic adjustment - Standard temperature deviation	1,2 °C
Stabilization time	3 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,05 g

Approval	
CE mark	✓
Accuracy classe	II
Verification scale interval [e]	0,1 g
Verification scale interval [e] (ct)	1 ct
Conformity assessment possible ex works	✓

Display	
Display type	LCD graphic
Display screen size	132×38 mm
Display backlight	✓
Display digit height - smallest digit	4 mm
Display digit height	15 mm
Languages of the user interface	English

Construction	
Dimension housing (W×D×H)	210×340×120 mm
Dimensions completely mounted (W×D×H)	210×340×120 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (Ø)	160 mm
Transport safety lock - bolt torque	0,1 Nm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6
Auto-off interval(s) in mains power mode	off 5 min 2 min 15 min
Capacity - Display	✓
Time display	✓
Tare function	manual (multi)
Density determination	✓

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PLJ

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Force compensation
Weighing capacity [Max]	6200 g
Weighing capacity [Max] (ct)	31000 ct
Readability [d]	0,01 g
Readability carat [d] (ct)	0,1 ct
Resolution	620.000
Linearity	± 0,05 g
Reproducibility	0,01 g
Tare range	6200 g
Default unit	g

	g
	mg
	gn
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo
	lb
	oz
Units (if device is conformity assessed)	g ct
Minimum weight [Min]	0,5 g

KERN PLJ 6200-2AM



Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples

Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Recipe/summing level	Rez B (Net-total, memory with plain text designations + setpoint, also for printout)
Recipe weighing - number of database entries	99
Recipe weighing - number of ingredients per database entry	20
Sum memory function	✓
Underfloor weighing	None
Interfaces	RS-232 standard

Counting

Smallest piece weight when piece counting - laboratory conditions	10 mg
Smallest piece weight when piece counting - normal conditions	100 mg
Counting reference weight can be entered	✓
Reference quantity	10, 25, 50, 100, n (any number of pieces)
Counting resolution (laboratory conditions)	620.000

Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	24 V; 1 A
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
	EURO
Plug-in power supply / adapter for countries - included with the delivery	AUS UK US CH
	EURO
Plug-in power supply / adapter for countries - optional	UK US CH

Environmental conditions

Humidity of environment [Max]	80 %
-------------------------------	------

Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	520×360×415 mm
Net weight	5,1 kg
Shipping method	Parcel service
Net weight approx.	6 kg
Gross weight approx.	8 kg
Shipping weight	15,5 kg

Services (optional)

Article number for conformity assessment	965-217
Article number for DAkkS calibration	963-104
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION



FACTORY

