


# KERN PLS 20000-1F

# KERN

High-quality precision scale with comfortable graphic display and enormous weighing range



Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,4 g
Maximum creep (15 minutes)	1 g
Maximum creep (30 minutes)	2 g

Approval	
CE mark	✓

Display	
Display type	LCD graphic
Display screen size	132×38 mm
Display backlight	✓
Display digit height - smallest digit	4 mm
Display digit height	15 mm
Languages of the user interface	English

Construction	
Dimension housing (W×D×H)	210×340×120 mm
Dimensions weighing platform (W×D×H)	200×175×15 mm
Dimensions completely mounted (W×D×H)	210×340×120 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	200×175 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6
	off
Auto-off interval(s) in mains power mode	5 min 2 min 15 min
Capacity - Display	✓
Time display	✓
PreTare function	✓
Tare function	manual (multi)
Density determination	✓
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Standby function	✓

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PLS

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	20000 g
Weighing capacity [Max] (ct)	100000 ct
Readability [d]	0,1 g
Readability carat [d] (ct)	1 ct
Resolution	200.000
Linearity	± 0,4 g
Reproducibility	0,1 g
Default unit	g
	g
	dwt
	tl (Tw)
	tl (HK)
	ozt
Units	tl (Singap, Malays)
	ct
	mo
	lb
	oz
USP Minimum weight of sample (k = 2, U = 0.1%)	200 g
Adjustment options	Adjusting with external weight
Recommended adjusting weight	20 kg (E2)
Possible calibration points	20 kg; 10 kg
Stabilization time	3 s

# KERN PLS 2000-1F

High-quality precision scale with comfortable graphic display and enormous weighing range

Recipe/summing level	Rez B (Net-total, memory with plain text designations + setpoint, also for printout)
Recipe weighing - number of database entries	99
Recipe weighing - number of ingredients per database entry	20
Underfloor weighing	Eye (included in delivery)
Interfaces	RS-232 standard

## Counting

Smallest piece weight when piece counting - laboratory conditions	500 mg
Smallest piece weight when piece counting - normal conditions	5 g
Counting reference weight can be entered	✓
Reference quantity	10, 25, 50, 100, n (any number of pieces)
Counting resolution (laboratory conditions)	40.000

## Power Supply

Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	9 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	450×320×300 mm
Net weight	3,2 kg
Shipping method	Parcel service
Net weight approx.	3,2 kg

Gross weight approx.	4,4 kg
Shipping weight	8,6 kg

## Services (optional)

Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

## Pictograms

### STANDARD



### OPTION

