## KERN SXC 100K-2L



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory



Category	
Brand	KERN
Product categoriy	Industrial scale
Product group	Stainless steel platform scale
Product family	SXC
Measuring System	
Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	150 kg
Readability [d]	0,01 kg
Resolution	15.000
Linearity	± 0,03 kg
Reproducibility	0,01 kg
Default unit	kg
Units	kg g Ib ffa PCS %
Adjustment options	Adjusting with external weight
Recommended adjusting weight	150 kg (M1)
Stabilization time	3 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,05 kg
Maximum creep (15 minutes)	40 g
Maximum creep (30 minutes)	80 g
Loadcell type	stainless steel IP68 encapsulated
Load cell connection	6-wire

pproval E mode	
CE mark	<i>√</i>
Display	
Display type	LCD
Display type	LCD with backlight
Display screen size	160×60 mm
Display backlight	1
Display digit height	48 mm
Languages of the user interface	English Symbol language
Construction	
Dimension display device (W×D×H)	232×150×80 mm
Dimensions weighing platform (W×D×H)	650×500×139 mm
Material display housing	stainless steel
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	650×500 mm
Cable length	3 m
Display device cable length	3 m
Allowed cable length display device [Max]	20 m
Material load cell(s)	Stainless steels
Load cells - number	1
Levelling feet adjustable	1
Wall mount	$\checkmark$
Functions	
Number of keys for operation	7
Auto-off interval(s) in mains power node	off
Auto-off interval(s) in battery node/rechargeable battery mode	5 min 2 min 1 min 30 min 60 min 30 sec
Capacity - Display	✓
PreTare function	1
Tare function	manual (multi)
Hold function	1
Percentage determination	1
Counting function	1
Folerance weighing	1

## KERN SXC 100K-2L



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	1
Recipe/summing level	Sum A
Sum memory function	1
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 (optional, factory) Ethernet (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory) Bluetooth BLE (v4.0) (optional, factory) USB-Device (optional, factory)
IP protection - complete device	-
IP protection - display	IP68
IP protection - load cell	IP68
IP protection - platform	no IP protection
Counting	
Smallest piece weight when piece counting - laboratory conditions	5 g
Smallest piece weight when piece counting - normal conditions	50 g
Counting reference weight can be entered	1
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	30.000
Power Supply	
Input voltage power supply / power [Max]	110 V - 240 V AC
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Rechargeable battery optional	Rchrg. battery optional - intern

Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Battery	no battery
Battery / accumulator type	Li-Ion
Environmental conditions	
Humity of environment [Min]	0 %
Humity of environment [Max]	80 %
Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	1050×675×250 mm
Net weight	33,5 kg
Shipping method	Parcel service
Net weight approx.	34 kg
Gross weight approx.	38 kg
Shipping weight	36,1 kg
Services (optional)	
Article number for adjustment at the location of installation	961-249
Article number for DAkkS calibration	963-129
Article number for certificate of conformity (verification)	969-517

## KERN SXC 100K-2L



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Pictograms

STANDARD



**OPTION** 



FACTORY

