KERN SXC 30K-3



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory



| Category | |
|-------------------|--------------------------------|
| Brand | KERN |
| Product categoriy | Industrial scale |
| Product group | Stainless steel platform scale |
| Product family | SXC |

| Measuring System | |
|--------------------------------|-----------------------------------|
| Construction type of the scale | Single-range balance |
| Number of weighing ranges | 1 |
| Weighing system | Strain gauge |
| Weighing capacity [Max] | 30 kg |
| Readability [d] | 0,002 kg |
| Resolution | 15.000 |
| Linearity | ± 0,006 kg |
| Reproducibility | 0,002 kg |
| Default unit | kg |
| Units | kg g Ib ffa PCS % |
| Adjustment options | Adjusting with external weight |
| Recommended adjusting weight | 30 kg (M1) |
| Stabilization time | 3 s |
| Warm-up time | 30 min |
| Eccentric loading at 1/3 [Max] | 0,01 kg |
| Maximum creep (15 minutes) | 8 g |
| Maximum creep (30 minutes) | 16 g |
| Loadcell type | stainless steel IP68 encapsulated |

| Load cell connection | 6-wire |
|--|--|
| Approval | |
| CE mark | ✓ |
| Display | |
| Display type | LCD |
| Display type | LCD with backlight |
| Display screen size | 160×60 mm |
| Display backlight | ✓ |
| Display digit height | 48 mm |
| Languages of the user interface | English Symbol language |
| Construction | |
| Dimension display device (W×D×H) | 232×150×80 mm |
| Dimensions weighing platform (W×D×H) | 400×300×111 mm |
| Material display housing | stainless steel |
| Material weighing plate | stainless steel |
| Material platform | Stainless steel |
| Dimensions weighing surface (W×D) | 300×240 mm |
| Display device cable length | 3 m |
| Allowed cable length display device [Max] | 20 m |
| Transport safety lock - bolt torque | 0,1 Nm |
| Material load cell(s) | Stainless steels |
| Load cells - number | 1 |
| Levelling feet adjustable | ✓ |
| Wall mount | ✓ |
| Functions | |
| Number of keys for operation | 7 |
| Auto-off interval(s) in mains power mode | off |
| Auto-off interval(s) in battery mode/rechargeable battery mode Capacity - Display | 5 min 2 min 1 min 30 min 60 min 30 sec |
| | v |

PreTare function

Counting function

Percentage determination

Tare function Hold function

1

manual (multi)

KERN SXC 30K-3

Tolerance weighing

delivery

Tolerance weighing - type of signal



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

acoustically

visual

| | visuai |
|---|--|
| Function for averaging under unstable weighing conditions | 1 |
| Recipe/summing level | Sum A |
| Sum memory function | ✓ |
| Alibi memory | optional internal memory |
| Alibi memory - number of memory spaces | 250.000 |
| Interfaces | RS-232 (optional, factory) Ethernet (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory) Bluetooth BLE (v4.0) (optional, factory) USB-Device (optional, factory) |
| IP protection - complete device | - |
| IP protection - display | IP68 |
| IP protection - load cell | IP68 |
| IP protection - platform | no IP protection |
| Counting | |
| Smallest piece weight when piece counting - laboratory conditions | 1 g |
| Smallest piece weight when piece counting - normal conditions | 10 g |
| Counting reference weight can be entered | 1 |
| Reference quantity | 5, 10, 20, 50, n (any number of pieces) |
| Counting resolution (laboratory conditions) | 30.000 |
| Power Supply | |
| Input voltage power supply / power [Max] | 110 V - 240 V AC |
| Plug-in power supply type | Built-in power supply |
| Supplied power supply | Power supply unit |
| Plug-in power supply / adapter for countries - included with the | EURO |

| Rechargeable battery optional | Rchrg. battery optional - intern |
|---|-------------------------------------|
| Rechargeable battery charging time | 8 h |
| Rechargeable battery operating time - backlight on | 20 h |
| Rechargeable battery operating time - backlight off | 48 h |
| Battery | no battery |
| Battery / accumulator type | Li-lon |
| Environmental conditions | |
| Humity of environment [Min] | 0 % |
| Humity of environment [Max] | 80 % |
| Ambient temperature [Min] | -10 °C |
| Ambient temperature [Max] | 40 °C |
| Packing & Shipping | |
| Readability force [d] (N) | 1 d |
| Dimensions packaging (W×D×H) | 800×465×225 mm |
| Net weight | 11,8 kg |
| | ,0 |
| Shipping method | Parcel service |
| · · · · · | |
| Net weight approx. | Parcel service |
| Net weight approx. Gross weight approx. | Parcel service 12 kg |
| Net weight approx. Gross weight approx. Shipping weight | Parcel service 12 kg 14 kg |
| Net weight approx. Gross weight approx. Shipping weight Services (optional) Article number for adjustment at | Parcel service 12 kg 14 kg |
| Net weight approx. Gross weight approx. Shipping weight Services (optional) Article number for adjustment at the location of installation Article number for DAkkS | Parcel service 12 kg 14 kg 16,7 kg |
| Shipping method Net weight approx. Gross weight approx. Shipping weight Services (optional) Article number for adjustment at the location of installation Article number for DAkkS calibration Article number for certificate of conformity (verification) | Parcel service 12 kg 14 kg 16,7 kg |

KERN SXC 30K-3



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Pictograms

STANDARD



OPTION



DMS 1 DAY

FACTORY

