

KERN SXC 30K-3L



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory



Category

Brand	KERN
Product category	Industrial scale
Product group	Stainless steel platform scale
Product family	SXC

Measuring System

Construction type of the scale	Single-range balance
Number of weighing ranges	1
Weighing system	Strain gauge
Weighing capacity [Max]	30 kg
Readability [d]	0,002 kg
Resolution	15.000
Linearity	± 0,006 kg
Reproducibility	0,002 kg
Default unit	kg

	kg
	g
Units	lb
	ffa
	PCS
	%

Adjustment options	Adjusting with external weight
Recommended adjusting weight	30 kg (M1)
Stabilization time	3 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,01 kg
Maximum creep (15 minutes)	8 g
Maximum creep (30 minutes)	16 g
Loadcell type	stainless steel IP68 encapsulated
Load cell connection	6-wire

Zulassung

CE mark	✓
---------	---

Display

Display type	LCD
Display type	LCD with backlight
Display screen size	160×60 mm
Display backlight	✓
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language

Construction

Dimension display device (W×D×H)	232×150×80 mm
Dimensions weighing platform (W×D×H)	500×400×120 mm
Material display housing	stainless steel
Material weighing plate	stainless steel
Material platform	Stainless steel
Dimensions weighing surface (W×D)	500×400 mm
Display device cable length	3 m
Allowed cable length display device [Max]	20 m
Transport safety lock - bolt torque	0,1 Nm
Material load cell(s)	Stainless steels
Load cells - number	1
Levelling feet adjustable	✓
Level indicator	✓
Wall mount	✓
Stand rotatable	no
Stand inclinable	no

Functions

Number of keys for operation	7
Auto-off interval(s) in mains power mode	off
	5 min
	2 min
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min
	30 min
	60 min
	30 sec
PreTare function	✓
Tare function	manual (multi)
Hold function	✓
Percentage determination	✓

KERN SXC 30K-3L



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Recipe/summing level	Sum A
Sum memory function	✓
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Interfaces	RS-232 (optional, factory) Ethernet (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory) Bluetooth BLE (v4.0) (optional, factory) USB-Device (optional, factory)
IP protection - complete device	-
IP protection - display	IP68
IP protection - load cell	IP68
IP protection - platform	no IP protection

Counting

Smallest piece weight when piece counting - laboratory conditions	1 g
Smallest piece weight when piece counting - normal conditions	10 g
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, n (any number of pieces)
Counting resolution (laboratory conditions)	30.000

Power Supply

Input voltage power supply / power [Max]	110 V - 240 V AC
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO

Rechargeable battery optional	Rchrg. battery optional (factory)
Rechargeable battery charging time	8 h
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	48 h
Battery	no battery
Battery / accumulator type	Li-Ion

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	490×790×235 mm
Net weight	20,8 kg
Shipping method	Parcel service
Net weight approx.	22 kg
Gross weight approx.	24 kg
Shipping weight	23,7 kg

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

KERN SXC 30K-3L



Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Pictograms

STANDARD



OPTION



FACTORY

