

Manual Test Stand SAUTER TVL-XS



Manual test stand for precise compressive force measurement in the range up to 100 N

Features

- **1** The redesigned, superfine spindle enables exact testing in a force-measurement range up to 100 N in particularly fine steps and, in conjunction with the fine-dosing crank, ensures safe, reliable operation
- **2** Main areas of application: Testing of low levels of force with short distances, such as, for example, testing keyboard overlays, biological samples (e.g. strength of leaves, etc.), blister packs (e.g. force required to push tablets out, etc.)
- For vertical and horizontal use
- High level of security at repeated measurements
- Large base plate with high versatility of fastening objects
- Suitable for all SAUTER force measuring devices with internal measuring cell up to 100 N (not included in delivery)

Technical data

- Travel distance per knob rotation (stroke per one turn): 2 mm
- Overall dimensions W×D×H 300×250×160 mm
- Net weight approx. 4,6 kg

Save with our practical bundles of test stand, force gauge and matching clamps, e.g. SAUTER TVL 100FHS71, consisting of:

- 1× TVL-XS
- 1× FH 100 (Details see page 14)
- 2× AE 500 (Details see page 43)

You can find our bundles on page 28/29

STANDARD



Model

Measuring range

SAUTER

[Max]
N

TVL-XS*

100

1 * ONLY WHILE STOCKS LAST

CAL EXT
Adjusting program (CAL)
 For quick setting of the instrument's accuracy. External adjusting weight required

CAL BLOCK
Calibration block
 Standard for adjusting or correcting the measuring device

PEAK
Peak hold function
 Capturing a peak value within a measuring process

SCAN
Scan mode
 Continuous capture and display of measurements

PUSH/PULL
Push and Pull
 The measuring device can capture tension and compression forces

SCALE
Length measurement
 Captures the geometric dimensions of a test object or the movement during a test process

FOCUS
Focus function
 Increases the measuring accuracy of a device within a defined measuring range

MEMORY
Internal memory
 To save measurements in the device memory

RS 232
Data interface RS-232
 Bidirectional, for connection of printer and PC

PROFIBUS
Profibus
 For transmitting data, e.g. between scales, measuring cells, controllers and peripheral devices over long distances. Suitable for safe, fast, fault-tolerant data transmission. Less susceptible to magnetic interference

PROFINET
Profinet
 Enables efficient data exchange between decentralised peripheral devices (balances, measuring cells, measuring instruments etc.) and a control unit (controller). Especially advantageous when exchanging complex measured values, device, diagnostic and process information. Savings potential through shorter commissioning times and device integration possible

USB
Data interface USB
 To connect the measuring instrument to a printer, PC or other peripheral devices

BT
Bluetooth* data interface
 To transfer data from the balance/measuring instrument to a printer, PC or other peripherals

WIFI
WIFI data interface
 To transfer data from the balance/measuring instrument to a printer, PC or other peripherals

IR
Data interface infrared
 To transfer data from the measuring instrument to a printer, PC or other peripheral devices

SWITCH
Control outputs (optocoupler, digital I/O)
 To connect relays, signal lamps, valves, etc.

ANALOG
Analogue interface
 To connect a suitable peripheral device for analogue processing of the measurements

DUAL
Analogue output
 For output of an electrical signal depending on the load (e.g. voltage 0 V - 10 V or current 4 mA - 20 mA)

LAN
Statistics
 Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.

SOFTWARE
PC Software
 To transfer the measurement data from the device to a PC

PRINT
Printer
 A printer can be connected to the device to print out the measurement data

LAN
Network interface
 For connecting the scale/measuring instrument to an Ethernet network

KCP PROTOCOL
KERN Communication Protocol (KCP)
 It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems

GLP PRINTER
GLP/ISO record keeping
 of measurement data with date, time and serial number. Only with SAUTER printers

UNIT
Measuring units
 Weighing units can be switched to e.g. non-metric. Please refer to website for more details

TOL
Measuring with tolerance range (limit-setting function)
 Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model

IP
Protection against dust and water splashes IPxx
 The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989 +A1:1999+A2:2013

ZERO
ZERO
 Resets the display to "0"

BATT
Battery operation
 Ready for battery operation. The battery type is specified for each device

ACCU
Rechargeable battery pack
 Rechargeable set

230 V
Plug-in power supply
 230V/50Hz in standard version for EU. On request GB, AUS or US version available

230 V
Integrated power supply unit
 Integrated, 230V/50Hz in EU. More standards e.g. GB, AUS or US on request

ELECTRO
Motorised drive
 The mechanical movement is carried out by an electric motor

STEPPER
Motorised drive
 The mechanical movement is carried out by a synchronous motor (stepper)

FAST-MOVE
Fast-Move
 The total length of travel can be covered by a single lever movement

M
Conformity assessment
 Models with type approval for construction of verifiable systems

DAkkS +3 DAYS
DAkkS calibration possible
 The time required for DAkkS calibration is shown in days in the pictogram

ISO +4 DAYS
Factory calibration (ISO)
 The time required for factory calibration is specified in the pictogram

1 DAY
Package shipment
 The time required for internal shipping preparations is shown in days in the pictogram

2 DAYS
Pallet shipment
 The time required for internal shipping preparations is shown in days in the pictogram

*The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Other trademarks and trade names are those of their respective owners.