

Motorised Vertical Test Stand SAUTER TVM-N · TVM-NL · TVM-LB






Motorised test stand incl. length measuring device LB

Test stand with electric motor for standard measurements – now also available as a set



Premium operating panel

- Digital speed display
- Digital repeat function



Control of the test stand using PC software SAUTER AFH



Solid and flexible fixing options for many clamps and accessories from the SAUTER product range, see *Accessories*

MEASURING TECHNOLOGY & TEST SERVICE 2024

Force measurement



Motorised Vertical Test Stand SAUTER TVM-N · TVM-NL · TVM-LB





Features

- Motorised test stand for tension/compression force testing
- NEW: Now also available as a practical set for force-displacement-measurements in laboratory and industry
- Set TVM-LB: Five in one motorised test stand, digital length measuring device LB, interface cable, data transfer software AFH FD, two interface converters AFH 12 and mounting
- Force controlled automatic switchoff, teststop after achieving an adjusted limit load, only in connection with a SAUTER FH force gauge
- Maximum displacement protected by electronic end switches
- SAUTER LA length measuring device as standard, to read the travel distance with a readability of 0,01 mm (only for TVM)
- Particularly flexible mounting options for variable force measuring devices, such as, SAUTER FC, FH, FK, FL:
 - ■ Direct mounting of measuring devices with internal load cell up to a measuring range of 500 N (only for TVM 5000N230N)
 - Direct mounting of the external load cell on the traverse, starting with 1000 N measurement range and higher
- Holder for force measuring devices of the SAUTER FH range with external load cell
- Set TVM-LB: With digital length measuring device LB for creating force-displacement diagrams on the PC, maximum measuring range 300 mm, readability 0,01 mm, for details see page 49

Technical data

- Maximum travel distance: 210 mm
- Speed accuracy: 3 % of [Max]

Accessories

- Only TVM: Data transfer software with graphic display of the measurement process, force-time, SAUTER AFH FAST
- In Holder for force measuring devices of the SAUTER FH range with external load cell, SAUTER TVM-A01
- Force gauges see page 11 et seq., clamps and other accessories see page 39 et seq.

STANDARD								
	· · · · · · · · · · · · · · · · · · ·		<u>@@</u>					
	•	VI.		70				
	SCALE	SOFTWARE	ELECTRO	2				
		TVM-LR						



Model	Measuring range	Speed range	Length of columns	
	[Max]	[Max]		
SAUTER	N	mm/min	mm	
TVM 5000N230N	5000	10 - 230	635	_
TVM 5000N230NL	5000	10 - 230	1135	
TVM 10KN120N	10000	30 - 120	1135	
TVM 20KN120N	20000	30 - 120	1135	
	Sets incl. test stand, length me	asuring device, interface cable, software	AFH FD, assembly:	
TVM 5000N230N-LB	5000	10 - 230	635	
TVM 5000N230NL-LB 🔤	5000	10 - 230	1135	
TVM 10KN120N-LB	10000	30 - 120	1135	
TVM 20KN120N-LB	20000	30 - 120	1135	

MEASURING TECHNOLOGY & TEST SERVICE 2024

SAUTER Pictograms



Conformity assessment

Models with type approval

DAkkS calibration

The time required for

DAkkS calibration is shown

Factory calibration (ISO)

The time required for factory

calibration is specified in

Package shipment

The time required for

internal shipping prepara-

tions is shown in days in

the pictogram

the pictogram

the pictogram

Pallet shipment

The time required for

internal shipping prepara-

tions is shown in days in

in days in the pictogram

systems

possible

for construction of verifiable

M

DAkkS

+3 DAYS

ISO

1 DAY



Adjusting program (CAL)

For quick setting of the instrument's accuracy. External adjusting weight required



Calibration block

Standard for adjusting or correcting the measuring



Peak hold function

Capturing a peak value within a measuring process



Scan mode

Continuous capture and display of measurements



Push and Pull

The measuring device can capture tension and compression forces



Length measurement

Captures the geometric dimensions of a test object or the movement during a test process



Focus function

Increases the measuring accuracy of a device within a defined measuring range



Internal memory

To save measurements in the device memory



Data interface RS-232

Bidirectional, for connection of printer and PC



Profibus

For transmitting data, e.g. between scales, measuring cells, controllers and peripheral devices over long distances. Suitable for safe, fast, fault-tolerant data transmission. Less susceptible to magnetic interference



Profinet

Enables efficient data exchange between de-centralised peripheral devices (balances, measuring cells, measuring instruments etc.) and a control unit (controller). Especially advantageous when exchanging complex measured values, device, diagnostic and process information. Savings potential through shorter commissioning times and device integration possible



Data interface USB

To connect the measuring instrument to a printer, PC or other peripheral devices



Bluetooth* data interface

To transfer data from the balance/measuring instrument to a printer, PC or other peripherals



WIFI data interface

To transfer data from the balance/measuring instrument to a printer, PC or other peripherals



Data interface infrared

To transfer data from the measuring instrument to a printer, PC or other peripheral devices



Control outputs (optocoupler, digital I/O) To connect relays, signal

lamps, valves, etc.



Analogue interface

To connect a suitable peripheral device for analogue processing of the measurements



Analogue output

For output of an electrical signal depending on the load (e.g. voltage 0 V - 10 V or current 4 mA - 20 mA)



Statistics

Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software

To transfer the measurement data from the device to a PC



Printer

A printer can be connected to the device to print out the measurement data



Network interface

For connecting the scale/ measuring instrument to an Ethernet network



KERN Communication Protocol (KCP)

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO record keeping

of measurement data with date, time and serial number. Only with SAUTER printers



Measuring units

Weighing units can be switched to e.g. non-metric. Please refer to website for more details



Measuring with tolerance range (limit-setting function)

Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model



Protection against dust and water splashes IPxx

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989 +A1:1999+A2:2013



ZERO

Resets the display to "0"



Battery operation

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack

Rechargeable set



Plug-in power supply 230V/50Hz in standard

version for EU. On request GB, AUS or US version available



Integrated power supply unit

Integrated, 230V/50Hz in EU. More standards e.g. GB, AUS or US on request



Motorised drive

The mechanical movement is carried out by a electric motor



Motorised drive

The mechanical movement is carried out by a synchronous motor (stepper)



Fast-Move

The total length of travel can be covered by a single lever movement



The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license Other trademarks and trade names are those of their respective owners