

# KERN TVM 20KN120N

# KERN

Test stand with electric motor for standard measurements



Type of drive	Electric motor
Guide column(s) length	113,5 cm
Guide column(s) distance	215 mm
Traverse distance [Max]	210 mm
Transversal movement speed [Min]	30 mm/min
Transversal movement speed [Max]	120 mm/min
Transversal movement speed variation	3%

## Functions

Speed display	✓
Repeat function	✓
Limit switch	✓

## Power Supply

Input voltage power supply / power [Max]	220 V AC, 50 Hz
Input voltage device / power [Max]	~220 V - 240 V AC; 50 Hz
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	EURO UK CH

## Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	520×345×1610 mm
Net weight	74 kg
Shipping method	Freight
Net weight approx.	75 kg
Gross weight approx.	90 kg
Shipping weight	88 kg

## Category

Brand	Sauter
Product category	Test bench
Product group	Motorised test stand
Product family	TVM

## Measuring System

Length measuring device	Length measuring device with display
-------------------------	--------------------------------------

## Approval

CE mark	✓
---------	---

## Display

Display type	LED segments
Display type	7 segment LED
Display digit height - smallest digit	9 mm
Display digit height	14 mm

## Construction

Dimension (W×D×H)	400×256×1535 mm
Dimension housing (W×D×H)	400×256×1535 mm
Dimensions completely mounted (W×D×H)	400×256×1535 mm
Material display housing	metal, lacquered
Material housing	metal, lacquered
Generated force [Max]	20 kN
Mounting - force application	Threaded hole - 1 × M12, 4 × M10
Mounting - force dissipation	Threaded hole M12 4 × threaded hole M10
Measurement alignment	vertical

# KERN TVM 20KN120N



Test stand with electric motor for standard measurements

## Pictograms

### STANDARD

---



### OPTION

---

