


# KERN TVO 500N500S

# KERN

Premium test stand in table-top version – with precise step motor



## Category

Brand	Sauter
Product category	Test bench
Product group	Motorised test stand
Product family	TVO-S

## Measuring System

Measurable length [Max]	30 cm
-------------------------	-------

## Approval

CE mark	✓
---------	---

## Display

Display type	LED segments
Display type	7 segment LED
Display digit height - smallest digit	9 mm
Display digit height	14 mm

## Construction

Dimension (W×D×H)	570×428×236 mm
Dimension housing (W×D×H)	570×428×236 mm
Dimensions completely mounted (W×D×H)	570×428×236 mm
Material display housing	Metal
Material housing	metal, lacquered
Generated force [Max]	500 N
Mounting - force application	5 × threaded hole M6
Mounting - force dissipation	5 × threaded hole M6
Measurement alignment	vertical
Type of drive	Stepper motor
Traverse distance [Max]	270 mm
Transversal movement speed [Min]	1 mm/min

Transversal movement speed [Max]	500 mm/min
----------------------------------	------------

Transversal movement speed variation	0,5%
--------------------------------------	------

## Functions

Speed display	✓
Repeat function	✓
Limit switch	✓

## Power Supply

Input voltage power supply / power [Max]	230 V AC, 50 Hz
Input voltage device / power [Max]	230 V AC, 50 Hz
Plug-in power supply type	Built-in power supply
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO

## Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Readability force [d] (N)	2 d
Dimensions packaging (W×D×H)	500×400×710 mm
Net weight	30 kg
Shipping method	Freight
Net weight approx.	30 kg
Gross weight approx.	40 kg
Shipping weight	40 kg

## Pictograms

### STANDARD



### OPTION

